

1


2

3

4

This document contains proprietary information and such information may not be disclosed to others for any purposes,
not used for sales/marketing/procurement purposes without written permission

REV	DESCRIPTION OF REVISION	ECN NO.	BY	DATE	APPROVED
A	Initial Release	—	H.wei	12/7/06	12/7/06



技术特性/Electrical Specifications

特性阻抗/Impedance
频率范围/Frequency Range
电压驻波比/VSWR
插入损耗/Insert Loss
耐压/Withstanding Voltage
绝缘电阻/Insulation Resistance

50 Ω
DC-18GHz
 ≤ 1.25
 $\leq 0.06 \text{xsqt. (f GHz)}$
 $\geq 750\text{V}$
 $\geq 5000\text{M}\Omega$

材料/Material Data

外导体/Outer contact
中心导体/Center contact
绝缘介质/Insulator

黄铜/Brass/三元合金/Temary alloy
镀青铜/Beryllium Bronze/金/Gold Plated
聚四氟乙烯/PTFE

连接参数/The connection parameters


内导体保持力/Center conductor retention $\geq 0.56\text{N}$
耐久性/durability ≥ 500 次(cycles)

环境参数/Environmental Data

温度范围/Temperature Range -55°C to 155°C

Notes:

- ALL SPECIFICATIONS ARE SUBJECT TO CHANGE NOTICE AT ANY TIME
- CUSTOMER OUTLINE DRAWING FOR REFERENCE ONLY

DRAWN: H.wei 12/07/06	TITLE: RF Coaxial Connector N Female Straight Flange Connector				
ENGINEER: L.yu 12/07/06					
APPROVED: W.yi 12/07/06		 DIMENSION IN MILLIMETERS (mm)			
TOLERANCES UNLESS OTHERWISE SPECIFIED .X ± 0.50 .X ± 0.20 .XX ± 0.10 ANGLES $\pm 1^{\circ}$					
PART NO: HL3-N-KFD-01	SIZE: A4	SCALE: N/A	SHEET: 1/1	REV: A	

1

2

3

4