


MSKSEMI 美森科

SEMICONDUCTOR




ESD



TVS



TSS



MOV



GDT



PLED

SPX1117M3-L-X-X/TR(MS)

Product specification

General Description

SPX1117M3-L-X-X/TR(MS) is a series of low dropout three-terminal regulators with a dropout of 1.3V at 1A load current. SPX1117M3-L-X-X/TR(MS) features a very low standby current 2mA compared to 5mA of competitor. Other than a fixed version, $V_{out} = 1.2V, 1.5V, 1.8V, 2.5V, 2.85V, 3.3V,$ and 5V, SPX1117M3-L-X-X/TR(MS) has an adjustable version, which can provide an output voltage from 1.25 to 12V with only two external resistors. SPX1117M3-L-X-X/TR(MS) offers thermal shut down function, to assure the stability of chip and power system. And it uses trimming technique to guarantee output voltage accuracy within 2%. Other output voltage accuracy can be customized on demand, such as 1%. SPX1117M3-L-X-X/TR(MS) is available in SOT-223.

Features

- Output current is 1A
- Range of operation input voltage: 15V
- Line regulation: 0.03%/V (typ.)
- Standby current: 2mA (typ.)
- Load regulation: 0.2%/A (typ.)
- Environment Temperature: $-40^{\circ}C \sim 85^{\circ}C$

Applications

- Power Management for Computer Mother Board, Graphic Card
- LCD Monitor and LCD TV
- DVD Decode Board
- ADSL Modem
- Post Regulators for Switching Supplies

Encapsulation form and pin definition function




Marking


<div style="background-color: black; color: white; padding: 5px; width: 100px; margin: 0 auto;"> MSKSEMI 1117M1V2 MS*** </div> SPX1117M3-L-1-2/TR(MS)	<div style="background-color: black; color: white; padding: 5px; width: 100px; margin: 0 auto;"> MSKSEMI 1117M1V5 MS*** </div> SPX1117M3-L-1-5/TR(MS)	<div style="background-color: black; color: white; padding: 5px; width: 100px; margin: 0 auto;"> MSKSEMI 1117M1V8 MS*** </div> SPX1117M3-L-1-8/TR(MS)	<div style="background-color: black; color: white; padding: 5px; width: 100px; margin: 0 auto;"> MSKSEMI 1117M2V85 MS*** </div> SPX1117M3-L-2-85/TR(MS)
<div style="background-color: black; color: white; padding: 5px; width: 100px; margin: 0 auto;"> MSKSEMI 1117M2V5 MS*** </div> SPX1117M3-L-2-5/TR(MS)	<div style="background-color: black; color: white; padding: 5px; width: 100px; margin: 0 auto;"> MSKSEMI 1117M3V3 MS*** </div> SPX1117M3-L-3-3/TR(MS)	<div style="background-color: black; color: white; padding: 5px; width: 100px; margin: 0 auto;"> MSKSEMI 1117M5V0 MS*** </div> SPX1117M3-L-5-0/TR(MS)	<div style="background-color: black; color: white; padding: 5px; width: 100px; margin: 0 auto;"> MSKSEMI 1117M3 MS*** </div> SPX1117M3-L/TR(MS)

Table1: SPX1117M3-L-X-X/TR(MS) series (SOT223 PKG)

PIN NO.	PIN NAME	FUNCTION
1	VSS/ADJ	VSS/ADJ pin
2	VOUT	Output voltage pin
3	VIN	Input voltage pin
4	VOUT	Output voltage pin



Block Diagram



Selection Table

Part No.	Part No.	Output Voltage	Package
SPX1117M3-L-X-X/TR(MS)	XX=12	1.2V	SOT-223
	XX=15	1.5V	
	XX=18	1.8V	
	XXX=285	2.85V	
	XX=25	2.5V	
	XX=33	3.3V	
	XX=50	5.0V	
	XX=ADJ	ADJ	

Ordering Information

Part No.	Package Type	Packing type
SPX1117M3-L-X-X/TR(MS)	SOT223	2500 Tape&Reel

Note: Xtands for Output Voltage

Absolute Maximum Ratings

Max Input Voltage	18V
Max Operating Junction Temperature(Tj)	150°C
Storage Temperature(Ts).....	-55°C~150°C
Lead Temperature & Time.....	260°C 10S

Caution: Exceed these limits to damage to the device. Exposure to absolute maximum rating conditions may affect device reliability.

Electrical Characteristics

T_A=25°C , unless otherwise noted.

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
V _{in}	Input voltage		--	15	18	V
V _{ref}	Reference voltage	SPX1117M3-L/TR(MS) 10mA≤I _{out} ≤1A , V _{in} =2.55V	1.225	1.25	1.275	V
V _{out}	Output voltage	SPX1117M3-L-1-2/TR(MS) 0≤I _{out} ≤1A , V _{in} =2.5V	1.176	1.2	1.224	V
		SPX1117M3-L-1-5/TR(MS) 0≤I _{out} ≤1A , V _{in} =2.8V	1.47	1.5	1.53	V
		SPX1117M3-L-1-8/TR(MS) 0≤I _{out} ≤1A , V _{in} =3.1V	1.764	1.8	1.836	V
		SPX1117M3-L-2-5/TR(MS) 0≤I _{out} ≤1A , V _{in} =3.8V	2.45	2.5	2.55	V
		SPX1117M3-L-2-85/TR(MS) 0≤I _{out} ≤1A , V _{in} =4.15V	2.793	2.85	2.907	V
		SPX1117M3-L-3-3/TR(MS) 0≤I _{out} ≤1A , V _{in} =4.6V	3.234	3.3	3.366	V
		SPX1117M3-L-5-0/TR(MS) 0≤I _{out} ≤1A , V _{in} =6.3V	4.9	5	5.1	V

ΔV _{out}	Line regulation	SPX1117M3-L-1-2/TR(MS) I _{out} =10mA, 2.5V≤V _{in} ≤10V		4	19	mV
		SPX1117M3-L-1-5/TR(MS) I _{out} =10mA, 2.8V≤V _{in} ≤10V		5	26	mV
		SPX1117M3-L/TR(MS) I _{out} =10mA, 2.55V≤V _{in} ≤12V		5	24	mV
		SPX1117M3-L-1-8/TR(MS) I _{out} =10mA, 3.1V≤V _{in} ≤12V		5	32	mV
		SPX1117M3-L-2-5/TR(MS) I _{out} =10mA, 3.8V≤V _{in} ≤12V		8	41	mV
		SPX1117M3-L-2-85/TR(MS) I _{out} =10mA, 4.15V≤V _{in} ≤12V		8	46	mV
		SPX1117M3-L-3-3/TR(MS) I _{out} =10mA, 4.6V≤V _{in} ≤12V		9	49	mV
		SPX1117M3-L-5-0/TR(MS) I _{out} =10mA, 6.3V≤V _{in} ≤12V		10	56	mV

ΔV_{out}	Load regulation	SPX1117M3-L-1-2/TR(MS) Vin =2.5V, 10mA \leq Iout \leq 1A	10	40	mV
		SPX1117M3-L-1-5/TR(MS) Vin =2.8V, 10mA \leq Iout \leq 1A	10	40	mV
		SPX1117M3-L/TR(MS) Vin =2.55V, 10mA \leq Iout \leq 1A	10	40	mV
		SPX1117M3-L-1-8/TR(MS) Vin =3.1V, 10mA \leq Iout \leq 1A	10	40	mV
		SPX1117M3-L-2-5/TR(MS) Vin =2.8V, 10mA \leq Iout \leq 1A	10	40	mV
		SPX1117M3-L-2-85/TR(MS) Vin =4.15V, 10mA \leq Iout \leq 1A	10	40	mV
		SPX1117M3-L-3-3/TR(MS) Vin =4.6V, 10mA \leq Iout \leq 1A	10	40	mV
		SPX1117M3-L-5-0/TR(MS) Vin =6.3V, 10mA \leq Iout \leq 1A	10	40	mV
Vdrop	Dropout voltage	Iout =100mA	1.15	1.3	V
		Iout=1A	1.3	1.5	V
Imin	Minimum load current	SPX1117M3-L/TR(MS)	2	10	mA
Iq	Quiescent Current	SPX1117M3-L-1-2/TR(MS), Vin=10V	2	5	mA
		SPX1117M3-L-1-5/TR(MS), Vin=10V	2	5	mA
		SPX1117M3-L-1-8/TR(MS), Vin=12V	2	5	mA
		SPX1117M3-L-2-5/TR(MS), Vin=12V	2	5	mA
		SPX1117M3-L-2-85/TR(MS), Vin=12V	2	5	mA
		SPX1117M3-L-3-3/TR(MS), Vin=12V	2	5	mA
		SPX1117M3-L-5-0/TR(MS), Vin=12V	2	5	mA
Iadj	Adjust pin current	SPX1117M3-L/TR(MS) Vin=5V, 10mA \leq Iout \leq 1A	55	120	μ A
Ichange	Iadj change	SPX1117M3-L/TR(MS) Vin=5V, 10mA \leq Iout \leq 1A	0.2	10	μ A

ΔV_{out}	Temperature coefficient	Vin=4.5V, Iout=10mA VOU=3.3V 20 $^{\circ}$ C \leq Ta \leq 120 $^{\circ}$ C	30		mV
θ_{JC}	Thermal resistance	SOT-223	20		$^{\circ}$ C/W

Note1: All test are conducted under ambient temperature 25 $^{\circ}$ C and within a short period of time 20ms

Note2: Load current smaller than minimum load current of SPX1117M3-L/TR(MS) will lead to unstable or oscillation output.

Detailed Description

SPX1117M3-L-X-X/TR(MS) is a series of low dropout voltage, three terminal regulators. Its application circuit is very simple: the fixed version only needs two capacitors and the adjustable version only needs two resistors and two capacitors to work. It is composed of some modules including start-up circuit, bias circuit, bandgap, thermal shutdown, power transistors and its driver circuit and so on.


The thermal shut down modules can assure chip and its application system working safety when the temperature is larger than 170°C.

The bandgap module provides stable reference voltage, whose temperature coefficient is compensated by careful design considerations. The temperature coefficient is under 100 ppm/°C. And the accuracy of output voltage is guaranteed by trimming technique.

Typical Application

SPX1117M3-L-X-X/TR(MS) has an adjustable version and six fixed versions (1.2V, 1.5V, 1.8V, 2.5V, 2.85V, 3.3V and 5V)


Fixed Output Voltage Version



Application circuit of SPX1117M3-L-X-X/TR(MS) fixed version

- (1) Recommend using 10uF tan capacitor as bypass capacitor (C1) for all application circuit.
- (2) Recommend using 10uF tan capacitor to assure circuit stability.

Adjustable Output Voltage Version



Application Circuit of SPX1117M3-L/TR(MS)

The output voltage of adjustable version follows the equation: $V_{out} = 1.25 \times (1 + R_2/R_1) + I_{Adj} \times R_2$. We can ignore I_{Adj} because I_{Adj} (about 50uA) is much less than the current of R_1 (about 2~10mA).




1) To meet the minimum load current (>10mA) requirement, R_1 is recommended to be 125ohm or lower. As SPX1117M3-L/TR(MS) can keep itself stable at load current about 2mA, R_1 is not allowed to be higher than 625ohm.

2) Using a bypass capacitor (C_{ADJ}) between the ADJ pin and ground can improve ripple rejection. This bypass capacitor prevents ripple from being amplified as the output voltage is increased. The impedance of C_{ADJ} should be less than R_1 to prevent ripple from being amplified. As R_1 is normally in the range of 100Ω~500Ω, the value of C_{ADJ} should satisfy this equation: $1/(2\pi \times f_{ripple} \times C_{ADJ}) < R_1$.

Thermal Considerations


We have to take heat dissipation into great consideration when output current or differential voltage of input and output voltage is large. Because in such cases, the power dissipation consumed by AMS1117 is very large. SPX1117M3-L-X-X/TR(MS) series uses SOT-223 package type and its thermal resistance is about 20°C/W. And the copper area of application board can affect the total thermal resistance. If copper area is 5cm*5cm (two sides), the resistance is about 30°C/W. So the total thermal resistance is about 20°C/W + 30°C/W. We can decrease total thermal resistance by increasing copper area in application board. When there is no good heat dissipation copper are in PCB, the total thermal resistance will be as high as 120°C/W, then the power dissipation of SPX1117M3-L-X-X/TR(MS) could allow on itself is less than 1W. And furthermore, SPX1117M3-L-X-X/TR(MS) will work at junction temperature higher than 125°C under such condition and no lifetime is guaranteed.

SOT-223 PACKAGE MECHANICAL DATA



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	—	1.800	—	0.071
A1	0.020	0.100	0.001	0.004
A2	1.500	1.700	0.059	0.067
b	0.660	0.840	0.026	0.033
b1	2.900	3.100	0.114	0.122
c	0.230	0.350	0.009	0.014
D	6.300	6.700	0.248	0.264
E	6.700	7.300	0.264	0.287
E1	3.300	3.700	0.130	0.146
e	2.300(BSC)		0.091(BSC)	
L	0.750	—	0.030	—
θ	0°	10°	0°	10°

Suggested Pad Layout



Note:

1. Controlling dimension: in millimeters.
2. General tolerance: ± 0.050 mm.
3. The pad layout is for reference purposes only.

Attention

- Any and all MSKSEMI Semiconductor products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your MSKSEMI Semiconductor representative nearest you before using any MSKSEMI Semiconductor products described or contained herein in such applications.
- MSKSEMI Semiconductor assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all MSKSEMI Semiconductor products described or contained herein.
- Specifications of any and all MSKSEMI Semiconductor products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- MSKSEMI Semiconductor strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all MSKSEMI Semiconductor products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of MSKSEMI Semiconductor.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. MSKSEMI Semiconductor believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the MSKSEMI Semiconductor product that you intend to use.