

■ Features

- Glass passivated chip
- Low reverse leakage current
- High surge current capability
- Fast reverse recovery time

■ Applications

- General purpose use in AC/DC bridge full wave rectification

■ Mechanical Data

- Case: D3K
- Polarity symbols being marked on body
- Molding compound meets UL 94V-0 flammability rating
- RoHS-compliant, Solder plated, solderable per MIL-STD-750, Method 2026




Reverse Voltage

50-1000 V

Forward Current

8.0 A max

Appearance Image



■ Marking

- RD8UB(05~10)

■ Maximum Ratings @ Ta = 25°C unless otherwise noted

PARAMETER	SYMBOL	UNIT	RD8UB05	RD8UB10	RD8UB20	RD8UB40	RD8UB60	RD8UB80	RD8UB100
Repetitive peak reverse voltage	V _{RRM}	V	50	100	200	400	600	800	1000
Maximum RMS voltage	V _{RMS}	V	35	70	140	280	420	560	700
Maximum DC blocking Voltage	V _{DC}	V	50	100	200	400	600	800	1000
Maximum average output current@60Hz sine wave, resistance load	I _{F(AV)}	A	8.0						
Peak forward surge current 8.3 ms single half sine wave superimposed on rated load	I _{FSM}	A	170						
Peak forward surge current 1.0 ms single half sine wave superimposed on rated load		A	340						
Current squared time @1ms≤t<8.3ms Tj=25℃, Rating of per diode	I²t	A²S	119.94						
Maximum reverse recovery time	T _{rr}	ns	150				250	500	
Storage temperature	T _{stg}	℃	-55~+150						
Junction temperature	T _j	℃	-55~+150						

■ Electrical Characteristics @ Ta = 25°C unless otherwise noted

PARAMETER	TEST CONDITIONS	SYMBOL	UNIT	RD8UB05	RD8UB10	RD8UB20	RD8UB40	RD8UB60	RD8UB80	RD8UB100
Maximum instantaneous forward voltage	$I_F=4.0A$	V_F	V	1.3						
Maximum DC reverse current at rated DC blocking voltage	$V_R=V_{DC}$, Tj=25°C	I_R	μA	5						
	$V_R=V_{DC}$, Tj=100°C	I_R		100						

■ Characteristic Curve (Typical)




FIG1. Derating Curve For Output Rectified Current




FIG2. Surge Forward Current Capability




FIG3. Typical Forward Characteristics





FIG4. Typical Reverse Characteristics


■ Marking and packet information



RD8UB*** : Marking Model **TOS** : Brand Logo

Packaging information	
每盒	500PCS
每箱	5000PCS
脚长定制	支持

■ D3K Package outline dimensions



Dimensions in millimeters

■ Notice

XILONG reserves the right to make modifications,enhancements,improvements,corrections or other changes without further notice to any producttherein.
xilong does not assume any liability arising out of the application or use of any product described herein.