

■ Features

- Glass passivated chip
- Low reverse leakage current
- High surge current capability
- Reliable low cost construction utilizing molded plastic technique

■ Mechanical Data

- Case: SGBJ
- Polarity symbols being marked on body
- Molding compound meets UL 94V-0 flammability rating
- RoHS-compliant, Solder plated, solderable per MIL-STD-750, Method 2026



■ Marking

- SGBJ35xx(08~16)

■ Maximum Ratings @ Ta = 25°C unless otherwise noted

PARAMETER	SYMBOL	UNIT	SGBJ3508	SGBJ3510	SGBJ3512	SGBJ3514	SGBJ3516
Repetitive peak reverse voltage	V_{RRM}	V	800	1000	1200	1400	1600
Maximum RMS voltage	V_{RMS}	V	560	700	840	980	1120
Maximum DC blocking Voltage	V_{DC}	V	800	1000	1200	1400	1600
Maximum average output current@60Hz sine wave, resistance load	$I_{F(AV)}$	A	35.0				
Peak forward surge current 8.3 ms single half sine wave superimposed on rated load	I_{FSM}	A	450				
Peak forward surge current 1.0 ms single half sine wave superimposed on rated load		A	900				
Current squared time @1ms≤t<8.3ms Tj=25°C, Rating of per diode	I^2t	A ² S	840.38				
Isolation Breakdown Voltage AC 50Hz/60Hz; R.M.S; 1min	V_{ISO}	V	2500				
Mounting Torque (Recommended torque:0.65 N·m)	M_s	N.m	0.8				
Storage temperature	T_{stg}	°C	-55~+150				
Junction temperature	T_j	°C	-55~+150				

■ Electrical Characteristics @ Tj = 25°C unless otherwise noted

PARAMETER	TEST CONDITIONS	SYMBOL	UNIT	SGBJ3508	SGBJ3510	SGBJ3512	SGBJ3514	SGBJ3516
Maximum instantaneous forward voltage	$I_F=17.5A$	V_F	V	1.1				
Maximum DC reverse current at rated DC blocking voltage	$V_R=V_{DC}$, Tj=25°C	I_R	μA	5				
	$V_R=V_{DC}$, Tj=100°C	I_R		500				


Reverse Voltage

800-1600 V

Forward Current

35.0 A max

Appearance Image



■ Characteristic Curve (Typical)




FIG1. Derating Curve For Output Rectified Current




FIG2. Surge Forward Current Capability




FIG3. Typical Forward Characteristics





FIG4. Typical Reverse Characteristics



■ Marking and packet information



SGBJ**** : Marking Model **TOS** : Brand Logo

Packaging information	
每盒	200PCS
每箱	1200PCS
脚长定制	支持

■ SGBJ Package outline dimensions



Dimensions in millimeters

■ Notice

XILONG reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein.
xilong does not assume any liability arising out of the application or use of any product described herein.