

30-Ampere, 45-200'Voltage'Schottky'Barrier'Metal-Silicon'Rectifiers

■ **Features**


- Metal silicon junction
- Low power loss and high efficiency
- Super fast reverse recovery time
- High surge current capability
- The plastic case material has UL flammability classification rating 94V-0

■ **Mechanical Data**

- Polarity: As marked
- Lead free complies with the EU ROHS directive
- Terminals: Tin plated leads, solderable per Mil-STD-750 Method 2026

■ **Typical applications**

- For use in general purpose rectification of power supplies, inverters, converters and freewheeling diodes for consumer, and telecommunication.



■ **Maximum Ratings @ Ta = 25°C unless otherwise noted**

PARAMETER		SYMBOL	MBR3045***	MBR30100***	MBR30150***	MBR30200***	UNIT
Maximum recurrent peak reverse voltage		V_{RRM}	45	100	150	200	V
Maximum RMS voltage		V_{RSM}	31.5	70	105	140	V
Maximum DC Blocking Voltage		V_{DC}	45	100	150	200	V
Maximum average forward rectified current	Per diode	I_{FM}	7				A
	Per device	I_{FM}	30				
Peak forward surge current 8.3 ms single half sine wave superimposed on rated load		I_{FSM}	120				A
Peak forward surge current 1.0 ms single half sine wave superimposed on rated load			400				A
Current squared time @1ms≤t<8.3ms Tj=25°C, Rating of per diode		I^2t	41.50				A²S
Maximum instantaneous forward voltage @IF=IFM (Per diode)		V_F	0.7	0.85	0.90	0.95	V
Maximum DC reverse current at rated DC blocking voltage	Tj=25°C	I_R	0.2				mA
	Tj=100°C	I_R	20				mA
Junction temperature range		T_j	-55~+150				°C
Storage temperature range		T_{STG}	-55~+150				°C

■ Characteristic Curve




FIG1. Forward Current Derating Curve




FIG2. Maximum Non-Repetitive Peak Forward Surge Current




FIG3. Typical Forward Voltage Characteristics






FIG4. Typical Reverse Characteristics


■ Package Outline Dimensions (TO-220F)



■ Package Outline Dimensions (TO-220AB)




■ Package Outline Dimensions (TO-252)



Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	2.1	2.6	0.083	0.102
A1	-	0.15	-	0.006
A2	2.0	2.5	0.079	0.098
B	1.1	1.6	0.043	0.063
b	0.5	0.8	0.020	0.031
b1	0.6	0.9	0.024	0.035
C	0.3	0.6	0.012	0.024
C1	0.3	0.6	0.012	0.024
D	6.1	6.7	0.240	0.264
D1	5.0	5.6	0.197	0.220
E	5.2	5.8	0.205	0.228
e	2.1	2.5	0.083	0.098
e1	4.2	4.9	0.165	0.193
L	9.5	10.5	0.374	0.413
L1	2.5	3.5	0.098	0.138
L2	1.2	1.8	0.047	0.071
L3	0.8	1.5	0.031	0.059
θ	0°	10°	0°	10°

■ Package Outline Dimensions (TO-263)




Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A1	0	0.3	0.000	0.012
B	1.3	1.4	0.051	0.055
b	0.7	0.8	0.028	0.031
b1	1.3	1.5	0.051	0.059
b2	0.7	0.8	0.028	0.031
C	4.4	4.7	0.173	0.185
C1	1.1	1.3	0.043	0.051
C2	2.5	2.8	0.098	0.110
C3	0.3	0.4	0.012	0.016
D	9.5	10.5	0.374	0.413
E	9.5	10.5	0.374	0.413
e	2.4	2.6	0.094	0.102
L	13.5	16.0	0.531	0.630
L1	4.5	5.5	0.177	0.217
L2	2.0	3.0	0.079	0.118
L3	1.0	1.6	0.039	0.063
θ	5°	10°	5°	10°

■ **Ordering information**

Package	Order code	Base quantity	Box quantity	Carton quantity
TO-220F/ITO-220AB	MBR10***FCT	50pcs/tube	1000pcs/box	5000pcs/cartoon
TO-220/TO-220AB	MBR10***CT	50pcs/tube	1000pcs/box	5000pcs/cartoon
TO-263	MBR10***DC	800pcs/reel	1600pcs/box	8000pcs/cartoon
TO-252	MBR10***CS	2500pcs/reel	5000pcs/box	25000pcs/cartoon

■ **Suggested thermal profiles for soldering processes**



Notice

XILONG reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. xilong does not assume any liability arising out of the application or use of any product described herein.