



NOTES:

备注

1. Copper, nickel base, matte tin  
黄铜H62, 镍底, 镀雾锡
2. Wire screw hole M4  
压线螺孔M4
3. Current Rating: 45A  
额定电流: 45A
4. Operating temperature: -40°C ~ +125°C  
工作温度: -40°C ~ +125°C
5. There shall be no defects such as pin deformation and burrs.  
不得有脚变形, 毛刺等缺陷
6. Unmarked dimensions refer to tolerances  
未标注的尺寸参考公差

Ordering Information

HC	-	*	**	*	*	-	****	-	D	***	*	-	02
Type		Thickness	Screw Thread	Welding Feet	Series	D-DIP	Product No.	Material					
M=Full Teeth (抽牙)		08-0.8mm	3=№3 (螺牙)	3=脚 (焊脚)	0808=8x8mm	S=SMT	产品序号	默认=Copper (黄铜)					
RW=Rivet Nut (铆螺母)		10-1.0mm	4=№4 (螺牙)	4=脚 (焊脚)	1620=16x20mm	FD=Flag Dip		RC=Red Copper (紫铜)					
		12-1.2mm	5=№5 (螺牙)	2=2个	.....								
		15-1.5mm	6=№6 (螺牙)	4=4个									
		20-2.0mm		6=6个									
		25-2.5mm		8=8个									
		30-3.0mm		.....									
		32-3.2mm											

			GENEAL TOLERANCE	制图 DRAWING	02	深圳市华灿天禄电子有限公司 ShenzhenhuaciantianluELECTRONICS CO.,LTD			
			DIM TOL	审核 CHECK		产品名称 TITLE	PCB 焊接端子 厚度0.8 插板 铆垫片 M4 4焊脚 8x8x8.3mm	版本 REV.	A
			5 or more ±0.35	批准 APPROVAL		产品料号 PART NO.	HC-RG0844-0808-D052-02	单位 UNITS	mm
1	初版发行		2~5 ±0.25	比例 SCALE		材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	0~2 ±0.15	投影 Projection					
			Angle ±3.0°						