




NOTES:

备注

1. Brass or purple copper, Bright tin-plating
黄铜或紫铜, 镀亮锡
2. Wire screw hole M5
压线螺孔M5
3. Current Rating: 70A
额定电流: 70A
4. There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
5. Unmarked dimensions refer to tolerances
未标注的尺寸参考公差



Ordering Information

HC - * ** * - **** - * ** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series	D=DF	Product No.	Material
M-Full Teeth (插牙)	08=0.8mm	3=M3 (螺牙)	4=M4 (螺牙)	0808=8x8mm	S=SMT	产品序号	默认=Copper (黄铜)
R=Right Nut (螺母)	10=1.0mm	4=M4 (螺牙)	5=M5 (螺牙)	1620=16x20mm	FP=Flag Dip		RC=Red Copper (紫铜)
B=Right Gasket (铆垫片)	15=1.5mm	5=M5 (螺牙)	6=M6 (螺牙)			
	20=2.0mm	6=M6 (螺牙)				
	25=2.5mm					
	30=3.0mm						
	32=3.2mm						

			GENEAL TOLERANCE	制图 DRAWING	07	深圳市华灿天禄电子有限公司 ShenzhenhuaciantianluELECTRONICS CO.,LTD			
			DIM TOL	审核 CHECK					
			5 or more ±0.35	批准 APPROVAL		产品料号 PART NO.	HC-RG1254-1109-D508-07	单位 UNITS	mm
1	初版发行		2~5 ±0.25	比例 SCALE		材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	0~2 ±0.15	投影 Projection					
			Angle ±3.0°						