




NOTES:

备注

1. Brass or purple copper, tin-plating
黄铜或紫铜, 镀锡
2. Wire screw hole M5
压线螺孔M5
3. Current Rating: 60A
额定电流: 60A
4. The maximum torque of the screw hole: 2.03 N/m
螺孔最大扭力: 2.03 N/m
5. Operating Temperature: -40°C~+125°C
工作温度: -40°C~+125°C
6. Has passed the 72 hour salt spray test
已通过72小时盐雾测试
7. There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
8. Unmarked dimensions refer to tolerances
未标注的尺寸参考公差



Ordering Information

HC - * ** * * - **** - D *** * - 07

| Type | Thickness | Screw Thread | Welding Feet | Series | DIP | Product No. | Material |
|-----------------------|--|--------------|--------------|----------------------------|-------------------------|-------------|---------------------------------------|
| W-hill Tooth (插子) | 08=0.8mm 10=1.0mm | 3=M3 (螺母) | 2=2个 | 0808=8x8mm 1620=16x20mm | S-SMT FD-Flag Dip | 产品序号 | 默认: Copper (黄铜) RC-Red Copper (紫铜) |
| RV-Rivet Nut (铆螺母) | 12=1.2mm 15=1.5mm | 4=M4 (螺母) | 4=4个 | | | | |
| RG-Rivet Gasket (铆垫片) | 20=2.0mm 25=2.5mm 30=3.0mm 32=3.2mm | 6=M6 (螺母) | 6=6个 8=8个 | | | | |

| | | | | | | | | | | |
|--------|---------------------|----------------|------------------|----------|----|---|------------------------|--|-------|-----|
| | | | GENEAL TOLERANCE | 制图 | 07 | 深圳市华灿天禄电子有限公司 ShenzhenhuaciantianluELECTRONICS CO.,LTD | | | | |
| | | | DIM TOL | 审核 | | | | | | |
| | | | 5 or more ±0.35 | 批准 | | 产品名称 | PCB 焊接端子 厚度1.2 插板 铆垫片 | | 版本 | A |
| | | | 2~5 ±0.25 | APPROVAL | | TITLE | M5 4焊脚 10.5x10x10.5mm | | REV. | |
| | | | 0~2 ±0.15 | 比例 | | 产品料号 | HC-RG1254-1010-D532-07 | | 单位 | mm |
| | | | Angle ±3.0° | 投影 | | PART NO. | | | 页次 | 1/1 |
| 序号 No. | 变更内容 MODIFY CONTENT | 日期 MODIFY DATE | | 材料 | | MATERIAL | | | SHEET | |