




NOTES:
备注


1. Brass or purple copper, Bright tin-plating
黄铜或紫铜, 镀亮锡
2. Wire screw hole M4
压线螺孔M4
3. Current Rating: 70A
额定电流: 70A
4. There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
5. Unmarked dimensions refer to tolerances
未标注的尺寸参考公差



Ordering Information

HC - * ** * - **** - * ** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series	Model	Product No.	Material
插脚 (Pin)	0.8±0.05mm	M4 (螺牙)	2脚	1620#16x20mm	插板 (Pin)	产品序号	黄铜 (Brass)
螺母 (Nut)	1.0±0.05mm	M4 (螺牙)	2脚	插板 (Pin)	紫铜 (Purple Copper)
螺帽 (Washer)	1.5±0.05mm	M4 (螺牙)	4脚	插板 (Pin)	紫铜 (Purple Copper)
螺垫圈 (Gasket)	2.0±0.05mm	M4 (螺牙)	6脚	插板 (Pin)	紫铜 (Purple Copper)
	2.5±0.05mm	M4 (螺牙)	8脚	插板 (Pin)	紫铜 (Purple Copper)
	3.0±0.05mm	M4 (螺牙)	插板 (Pin)	紫铜 (Purple Copper)



		GENERAL TOLERANCE		制图	07			
		DIM	TOL	审核	深圳市华灿天禄电子有限公司			
		5 or more	±0.35	CHECK	ShenzhenhuacantianluELECTRONICS CO.,LTD			
		2~5	±0.25	批准	产品名称	PCB 焊接端子 厚度1.2 插板 铆垫片	版本	A
		0~2	±0.15	APPROVAL	TITLE	M4 4焊脚 11x9x11.5mm	REV.	
1	初版发行			比例	产品料号	HC-RG1244-1109-D508-07	单位	mm
序号	变更内容	日期		SCALE	PART NO.		页次	1/1
No.	MODIFY CONTENT	MODIFY DATE		投影	MATERIAL		SHEET	

