

### Key Parameter Performance

Parameter	Value	Unit
$V_{DS}$	30	V
$R_{DS(on)}$ (max)	$V_{GS} = 10V$	24
	$V_{GS} = 4.5V$	34
$Q_g$	4.1	nC

### Pin Definition:

1. Gate
2. Source
3. Drain


### Note:

MSL 1 (Moisture Sensitivity Level)  
per J-STD-020

### Block Diagram



SOT-23



N-Channel MOSFET

### Absolute Maximum Ratings (T<sub>C</sub> = 25°C unless otherwise noted)

Parameter	Symbol	Limit	Unit
Drain-Source Voltage	$V_{DS}$	30	V
Gate-Source Voltage	$V_{GS}$	±20	V
Continuous Drain Current	$I_D$	T <sub>C</sub> = 25°C	6.5
		T <sub>C</sub> = 100°C	4.1
Pulsed Drain Current (Note 1)	$I_{DM}$	26	A
Single Pulse Avalanche Energy (Note 2)	$E_{AS}$	32	mJ
Power Dissipation @ T <sub>C</sub> = 25°C	$P_D$	1.56	W
Operating Junction Temperature	T <sub>J</sub>	-55 to +150	°C
Storage Temperature Range	T <sub>STG</sub>	-55 to +150	°C

### Thermal Performance

Parameter	Symbol	Limit	Unit
Thermal Resistance - Junction to Ambient	$R_{\theta JA}$	80	°C/W

**Electrical Specifications** ( $T_C = 25^\circ\text{C}$  unless otherwise noted)


Parameter	Conditions	Symbol	Min	Typ	Max	Unit
<b>Static</b>						
Drain-Source Breakdown Voltage	$V_{GS} = 0V, I_D = 250\mu A$	$BV_{DSS}$	30	--	--	V
Drain-Source On-State Resistance	$V_{GS} = 10V, I_D = 6A$	$R_{DS(on)}$	--	17	24	m $\Omega$
	$V_{GS} = 4.5V, I_D = 4A$		--	22	34	
Gate Threshold Voltage	$V_{DS} = V_{GS}, I_D = 250\mu A$	$V_{GS(TH)}$	1.2	1.4	2.5	V
Zero Gate Voltage Drain Current	$V_{DS} = 30V, V_{GS} = 0V$	$I_{DSS}$	--	--	1	$\mu A$
	$V_{DS} = 24V, T_J = 125^\circ\text{C}$		--	--	10	
Gate Body Leakage	$V_{GS} = \pm 20V, V_{DS} = 0V$	$I_{GSS}$	--	--	$\pm 100$	$\mu A$
Forward Transconductance (Note 3)	$V_{DS} = 10V, I_D = 4A$	$g_{fs}$	--	6.5	--	S
<b>Dynamic</b>						
Total Gate Charge (Note 3,4)	$V_{DS} = 15V, I_D = 6A,$ $V_{GS} = 4.5V$	$Q_g$	--	4.1	--	nC
Gate-Source Charge (Note 3,4)		$Q_{gs}$	--	1	--	
Gate-Drain Charge (Note 3,4)		$Q_{gd}$	--	2.1	--	
Input Capacitance	$V_{DS} = 25V, V_{GS} = 0V,$ $f = 1.0\text{MHz}$	$C_{iss}$	--	345	--	pF
Output Capacitance		$C_{oss}$	--	55	--	
Reverse Transfer Capacitance		$C_{rss}$	--	32	--	
<b>Switching</b>						
Turn-On Delay Time (Note 3,4)	$V_{DD} = 15V, I_D = 1A,$ $V_{GS} = 10V, R_G = 6\Omega$	$t_{d(on)}$	--	2.8	--	ns
Turn-On Rise Time (Note 3,4)		$t_r$	--	7.2	--	
Turn-Off Delay Time (Note 3,4)		$t_{d(off)}$	--	15.8	--	
Turn-Off Fall Time (Note 3,4)		$t_f$	--	4.6	--	
<b>Source-Drain Diode Ratings and Characteristic</b>						
Maximum Continuous Drain-Source Diode Forward Current	Integral reverse diode in the MOSFET	$I_S$	--	--	6.5	A
Maximum Pulse Drain-Source Diode Forward Current		$I_{SM}$	--	--	26	A
Diode-Source Forward Voltage	$V_{GS} = 0V, I_S = 1A$	$V_{SD}$	--	--	1	V

**Note:**


- Pulse width limited by safe operating area
- $L = 1\text{mH}, I_{AS} = 8A, V_{DD} = 25V, R_G = 25\Omega, \text{Starting } T_J = 25^\circ\text{C}$
- Pulse test: pulse width  $\leq 300\mu s$ , duty cycle  $\leq 2\%$
- Switching time is essentially independent of operating temperature.

**Electrical Characteristics Curve**


**Continuous Drain Current vs.  $T_c$**




**Gate Charge**




**On-Resistance vs. Junction Temperature**




**Threshold Voltage vs. Junction Temperature**



**Maximum Safe Operating Area**




**Normalized Thermal Transient Impedance Curve**



**Package information (Unit: mm)**

SOT-23



**Mounting Pad Layout (Unit: mm)**

