




SAMZO REAC/ROHS

REV	ECN NO	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	Replace frame			2018.06.12

技术要求:

Technical requirements:

1. 打铜底0.5-1UM, 镍底1-3UM, 哑锡3-5UM.
Copper base 0.5 - 1 UM, nickel base 1-3UM, matte tin 3 - 5 UM.
2. 不得有脚变形, 毛刺等缺陷。
There shall be no defects such as pin deformation and burrs.
3. 插脚尖部符合可焊性要求。
The tip of the insertion pin shall meet the solderability requirements.
4. 螺纹需符合通止规要求。
The thread shall meet the requirements of the go and no-go gauge.
5. 材质: 黄铜H62。
Material: Brass H62.
6. 过载电流: 100A
Overload current: 100A
7. 螺孔为 M5
The screw holes M5
8. 未标注尺寸公差值按GB/T1184-1996H级
Unmarked dimensional tolerance values are in accordance with Grade H of GB/T1184-1996
9. 螺丝扭力: 2.0Nm
Screw torque: 2.0Nm



1215 140 40 1 L5

Pressing hole specification: M5
 Mold number: C021-H
 Pin height: 4.0mm
 Height above the board: 14.0mm
 Specification size: 12.4*15mm

ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR					
A	Subject	H62(Y2)	1	tin plating					
					GENERAL TOLERANCE				
						DESIGN	WANGGUIFA	2018.06.12	≥0~2< ±0.15
						CHECKED	ZHENGUILAN	2018.06.12	≥2~5< ±0.25
						APPROVED	LILIANJIANG	2018.06.14	≥0~2< ±0.15
F									≥5 ±0.35

FIRST VIEW

SCALE: 1:1 UNIT: mm

SAMZO COMPONENTS
Electronic switch and connector manufacturer

The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.
WWW.KKK-JP.COM

TITLE: 12.4*15-H14+4mm 90° DIP (M5)	
DWG NO: 1215-PC030	
PART NO: 1215-2022001	
MODEL NO: 1215140401L5	
NAME: PCB soldering terminal	