



**SAMZO REAC/ROHS**

**技术要求:**



- Technical requirements:  
 1. 打铜底0.5-1UM,镍底2-2.5UM,亮锡3-5UM.  
 Copper Underlayer: 0.5 - 1 μm, Nickel Underlayer: 2-2.5 μm, Matte Tin: 3 - 5 μm  
 2. 不得有脚变形, 毛刺等缺陷。  
 There shall be no defects such as pin deformation and burrs.  
 3. 插脚尖部符合可焊性要求。  
 The tip of the insertion pin shall meet the solderability requirements.  
 4. 螺纹需符合通止规要求。  
 The thread shall meet the requirements of the go and no-go gauge.  
 5. 材质: 紫铜T2.  
 Material: Red copper T2.  
 6. 过载电流: 80A  
 Overload current: 80A  
 7. 牙孔规格 M5  
 The specification of the threaded hole M5  
 8. 未标注尺寸公差值按GB/T1184-1996H级  
 Unmarked dimensional tolerance values are in accordance with Grade H of GB/T1184-1996  
 9. 螺丝扭力: 2.0Nm  
 Screw torque: 2.0Nm  
 10. 盐雾试验: 48小时  
 Salt spray test: 48H

REV	ECN NO	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	Replace frame			2013.02.12



**911 85 40 2 D5**

Pressing hole specification: M5  
 Mold number: S001-T  
 Pin height: 4.0mm  
 Height above the board: 8.5mm  
 Specification size: 9.2\*11.2mm



ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR	FIRST VIEW				
A	Subject	Red copper T2	1	tin plating					
B	Gasket	SPCC	1	tin plating					
C	Washer	SPCC	1		GENERAL TOLERANCE		SCALE	UNIT	
					DESIGN	WANGGUIFA	2018.06.12	1:1	mm
					CHECKED	ZHENGUILAN	2018.06.12	<b>SAMZO COMPONENTS</b> Electronic switch and connector manufacturer	
F					APPROVED	LILIANJIANG	2018.06.14		

The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.  
 WWW.KKK-JP.COM

TITLE::	9.2*11.2*12.5mm 4pin DIP T2
DWG NO:	911T-P001
PART NO:	911T-16001
MODEL NO:	91185402D5
NAME:	PCB soldering terminal