


1		2		3		4		5		6		7		8	
SAMZO		REAC/ROHS								REV	ECN NO	DESCRIPTION	DESIGN	APPROVAL	DATE
										A1	NEW	Replace frame			2018.06.12

技术要求:
Technical requirements:
 1. 打铜底0.5-1UM, 镍底1-3UM, 哑锡3-5UM。
 Copper base 0.5 - 1 UM, nickel base 1-3UM, matte tin 3 - 5 UM.
 2. 不得有脚变形, 毛刺等缺陷。
 There shall be no defects such as pin deformation and burrs.
 3. 插脚尖部符合可焊性要求。
 The tip of the insertion pin shall meet the solderability requirements.

4. 螺纹需符合通止规要求。
 The thread shall meet the requirements of the go and no-go gauge.
 5. 材质: 黄铜H62。
 Material: Brass H62.
 6. 过载电流: 80A
 Overload current: 80A
 7. 螺孔为 M4
 The screw holes M4
 8. 未标注尺寸公差值按GB/T1184-1996H级
 Unmarked dimensional tolerance values are in accordance with Grade H of GB/T1184-1996

9. 螺丝扭力: 2.5Nm
 Screw torque: 2.5Nm



11 120 40 1 D4
 Pressing hole specification: M4
 Mold number: C036-H
 Pin height: 4.0mm
 Height above the board: 12.0mm
 Specification size: 11*11mm

A	ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR	FIRST VIEW				The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts. WWW.KKK-JP.COM	TITLE: 11*11-H12.0+4.0mm (M4)		
	A	Subject	H62(Y2)	1	tin plating	GENERAL TOLERANCE					DWG NO: 11120-P030		
	B	Gasket	SPCC	1	tin plating	SCALE	1:1	UNIT	mm		PART NO: 11120-202901		
						DESIGN	WANGGUIFA	2018.06.12	≥0~2<		±0.15	MODEL NO: 11120401D4	
						CHECKED	ZHENGUILAN	2018.06.12	≥0~2<		±0.15	NAME: PCB soldering terminal	
F					APPROVED	LILIANJIANG	2018.06.14	≥5	±0.35	SAMZO COMPONENTS Electronic switch and connector manufacturer			

1		2		3		4		5		6		7		8	
---	--	---	--	---	--	---	--	---	--	---	--	---	--	---	--