



SAMZO REAC/ROHS

技术要求:

Technical requirements:



- 打铜底0.5-1UM, 镍底1-3UM, 哑锡3-5UM。
Copper base 0.5 - 1 UM, nickel base 1-3UM, matte tin 3 - 5 UM.
- 不得有脚变形, 毛刺等缺陷。
There shall be no defects such as pin deformation and burrs.
- 插脚尖部符合可焊性要求。
The tip of the insertion pin shall meet the solderability requirements.
- 螺纹需符合通止规要求。
The thread shall meet the requirements of the go and no-go gauge.
- 材质: 黄铜H62。
Material: Brass H62.
- 过载电流: 60A
Overload current: 60A
- 螺孔为 M4
The screw holes M4
- 未标注尺寸公差值按GB/T1184-1996H级
Unmarked dimensional tolerance values are in accordance with Grade H of GB/T1184-1996
- 螺丝扭力: 1.5Nm
Screw torque: 1.5Nm



911 52 40 1 L4

- Pressing hole specification: M4
- Mold number: C038-H
- Pin height: 4.0mm
- Height above the board: 5.2mm
- Specification size: 9.2*11.1mm

REV	ECN NO	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	Replace frame			2018.06.12



PCB LAYOUT

ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR					
A	Subject	H62(Y2)	1	tin plating					
					GENERAL TOLERANCE				
					≥0~2<	±0.15			
					DESIGN	WANGGUIFA	2018.06.12	≥2~5<	±0.25
					CHECKED	ZHENGUILAN	2018.06.12	≥0~2<	±0.15
					APPROVED	LILIANJIANG	2018.06.14	≥5	±0.35

FIRST VIEW				The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts. WWW.KKK-JP.COM		TITLE: 9.2*11.1-H5.2+4.0mm (M4)	
						DWG NO: 91152-P032	
SCALE	1:1	UNIT	mm			PART NO: 91152-2018030	
SAMZO COMPONENTS Electronic switch and connector manufacturer						MODEL NO: 91152401L4	
						NAME: PCB soldering terminal	