



Part No	Pin	A	B	C
BX-SH1.0-2PWT	2	1.00	4.35	2.60
BX-SH1.0-3PWT	3	2.00	5.35	3.60
BX-SH1.0-4PWT	4	3.00	6.35	4.60
BX-SH1.0-5PWT	5	4.00	7.35	5.60
BX-SH1.0-6PWT	6	5.00	8.35	6.60
BX-SH1.0-7PWT	7	6.00	9.35	7.60
BX-SH1.0-8PWT	8	7.00	10.35	8.60
BX-SH1.0-9PWT	9	8.00	11.35	9.60
BX-SH1.0-10PWT	10	9.00	12.35	10.60
BX-SH1.0-11PWT	11	10.00	13.35	11.60
BX-SH1.0-12PWT	12	11.00	14.35	12.60
BX-SH1.0-13PWT	13	12.00	15.35	13.60
BX-SH1.0-14PWT	14	13.00	16.35	14.60
BX-SH1.0-15PWT	15	14.00	17.35	15.60
BX-SH1.0-16PWT	16	15.00	18.35	16.60
BX-SH1.0-20PWT	20	19.00	22.35	20.60

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.0
- 2.Voltage Rating: 50V AC DC
- 3.Current Rating: 1A AC DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 30mΩ Max
- 6.Withstanding voltage: 250V AC 1/Minute
- 7.Temperatuer Range: -40℃ ~+ 85℃

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-SH1.0-NPWT		版本 REV.	A
			X.±0.20	X'.:±5°	审核 CHECK	EVA		品名 TITLE	WAFER 1.00 贴片		页次 SHEET	1/1
			.X±0.10	X.X':±3°	核准 APPROVAL	JADE		客户料号 CUTM.NO.				
			.XX±0.05	X.XX':±1°	单位 UNITS	MM	比例 SCALE	1:1		Bossie (博锡)		