






D	02-10P	0.10	MAX
	11-16P	0.12	MAX



Part No	Pin	A	B	C	D	E
BX-HY2.0-2PWT	2	2.00	8.00	6.40	4.90	2.50
BX-HY2.0-3PWT	3	4.00	10.00	8.40	6.90	3.00
BX-HY2.0-4PWT	4	6.00	12.00	10.40	8.90	5.00
BX-HY2.0-5PWT	5	8.00	14.00	12.40	10.90	7.00
BX-HY2.0-6PWT	6	10.00	16.00	14.40	12.90	9.00
BX-HY2.0-7PWT	7	12.00	18.00	16.40	14.90	11.00
BX-HY2.0-8PWT	8	14.00	20.00	18.40	16.90	13.00
BX-HY2.0-9PWT	9	16.00	22.00	20.40	18.90	15.00
BX-HY2.0-10PWT	10	18.00	24.00	22.40	20.90	17.00
BX-HY2.0-11PWT	11	20.00	26.00	24.40	22.90	19.00
BX-HY2.0-12PWT	12	22.00	28.00	26.40	24.90	21.00
BX-HY2.0-13PWT	13	24.00	30.00	28.40	26.90	23.00
BX-HY2.0-14PWT	14	26.00	32.00	30.40	28.90	25.00
BX-HY2.0-15PWT	15	28.00	34.00	32.40	30.90	27.00
BX-HY2.0-16PWT	16	30.00	36.00	34.40	32.90	29.00

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 2.0
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 2A AC DC
- 4.Insulation Resistance: 800MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/ Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE	
			X.±0.20	X'.:±5°
			.X±0.10	X.X':±3°
			.XX±0.05	X.XX':±1°

制图 DRAWING	EMMA
审核 CHECK	EVA
核准 APPROVAL	JADE
单位 UNITS	MM
比例 SCALE	1:1

料号 PART NO.	BX-HY2.0-NPWT	版本 REV.	A
品名 TITLE	WAFER 2.00 贴片基板	页次 SHEET	1/1
客户料号 CUTM.NO.			

