


- 技术要求:
1. 塑件材料: PA66(UL-94V-0)
 2. 接触件: 黄铜镀锡
 3. 接触电阻: $\leq 10m\Omega$
 4. 绝缘电阻: $\geq 100M\Omega$
 5. 额定电压: 250V AC DC
 6. 额定电流: 2.0A AC DC
 7. 耐压: 能承受 1000V AC/Minute
 8. 工作温度: $-40^{\circ}\sim+85^{\circ}$
 9. 可焊性试验: 浸锡面积 $\geq 95\%$ 温度 $235^{\circ}\pm 5^{\circ}$, 时间 2.5 ± 0.5 秒
 10. 铅和镉等六大有害物质含量要符合环保要求。

| Part No | Pin | A | B |
|----------------|-----|-------|-------|
| BX-HY2.0-2PZZ | 2 | 2.00 | 6.00 |
| BX-HY2.0-3PZZ | 3 | 4.00 | 8.00 |
| BX-HY2.0-4PZZ | 4 | 6.00 | 10.00 |
| BX-HY2.0-5PZZ | 5 | 8.00 | 12.00 |
| BX-HY2.0-6PZZ | 6 | 10.00 | 14.00 |
| BX-HY2.0-7PZZ | 7 | 12.00 | 16.00 |
| BX-HY2.0-8PZZ | 8 | 14.00 | 18.00 |
| BX-HY2.0-9PZZ | 9 | 16.00 | 20.00 |
| BX-HY2.0-10PZZ | 10 | 18.00 | 22.00 |
| BX-HY2.0-11PZZ | 11 | 20.00 | 24.00 |
| BX-HY2.0-12PZZ | 12 | 22.00 | 26.00 |
| BX-HY2.0-13PZZ | 13 | 24.00 | 28.00 |
| BX-HY2.0-14PZZ | 14 | 26.00 | 30.00 |
| BX-HY2.0-15PZZ | 15 | 28.00 | 32.00 |



SUGGESTED PCB LAYOUT
(COMPONENT SIDE)

| 制图 DRAWN | 变更内容 DESCRIPTION | 日期 DATE | GENERAL TOLERANCE | |
|-------------|---------------------|------------|-------------------|-----|
| | | | X.±0.20 | ±2° |
| | | | .X±0.10 | |
| | | | .XX±0.05 | |

| | |
|----------------|------|
| 制图 DRAWING | EMMA |
| 审核 CHECK | EVA |
| 核准 APPROVAL | JADE |
| 单位 UNITS | MM |
| 比例 SCALE | 1:1 |

| | | | |
|------------------|------------------|-------------|-----|
| 料号 PART NO. | BX-HY2.0-NPZZ | 版本 REV. | A |
| 品名 TITLE | WAFER HY2.0MM 直插 | 页次 SHEET | 1/1 |
| 客户料号 CUTM.NO. | | | |

