

技术要求 Specification:

1、材质:磷青,表面镀锡,

Material: Phos. Bronze Tin-Plated

镀层: Sn > 2.50um, Ni > 0.50um

2、零件外观不得有有害毛刺、尖角、锐边和机械损伤:表面镀层应均匀、光亮、无雾斑、剥层等缺陷;



Parts may not have the appearance of harmful burrs, sharp corners, sharp edges and mechanical damage, surface coating should be uniform, bright, no fog spots, delamination and other defects.

3、适用线号: AWG#32-#28

Wirerange: AWG#32-#28

3、适用线号: AWG#32-#28:

Wirerange: AWG#32-#28

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	料号 PART NO.	BX-GH1.25-DZ	版本 REV.	A
			X.±0.20	X.*±1*	审核 CHECK	品名 TITLE	GH1.25MM TERMINAL	页次 SHEET	1/1
			.X±0.15		核准 APPROVAL	客户料号 CUTM.NO.			
			.XX±0.10		单位 UNITS	MM		比例 SCALE	1:1
						EMMA		 Bossie (博锡)	
						EVA			
						JADE			