






linear dimension (Tolerances Standard GB/T 14486-2008)	—									
variable range	6 to 6	over 6 to 10	over 10 to 30	over 30 to 60	over 60 to 100	over 100 to 160	over 160 to 10	over 10 to 100	over 100 to 100	over 100 to 100
tolerance	±0.20	±0.30	±0.50	±0.70	±1.00	±1.30	±1.60	0.10	0.30	0.60



UL/CUL 技术参数	UL/CUL Technical Data			eRus		
等级	Use Group	B	C	D		
额定电压	Rated Voltage	NV	300	-	300	
额定电流	Rated Current	IAI	16	-	10	
接线范围	Wire Range		22-12			
单/多芯线	Solid/Stranded	[AWG]				
耐电压	Withstanding Voltage		1600V/Min			
IEC 技术参数						
IEC Technical Data						
过电压类别	Overvoltage Category	III	III	II		
污染等级	Contamination Class	3	2	2		
额定电压	Rated Voltage	NV	250	400	630	
额定电流	Rated Current	IAI	20	20	20	
额定冲击电压	Impulse withstand voltage	[kV]	4	4	4	
导线截面积	Conductor cross section		2.5			
硬质/柔性导线	Solid/flexible	[mm ²]				
材料						
绝缘材料	Insulation Material	PA66				
阻燃等级	Inflammability	UL94V-0				
导体材料	Conductor Material	铜合金 Copper alloy				
导体表面处理层	Conductive Coating	镀锡 Sn Plated				
一般参数 Other Data						
间距 Pitch	[mm]	5.08				
极数 Poles	[P]	02-24				
剥线长度 Stripping Length	[mm]	6-7				
螺丝 Screw/扭矩 Torque(Max)	[N.m]	M2.5/0.4				
工作温度 Operating temperatur	[°C]	-40~+105				
引脚尺寸 Pin Dimensions	[mm]	0.80x1.05				
PCB板孔径 PCB Hole Diameter	[mm]	1.60				

DB128L — 5.08 — XXP — C — S/P

(Series No.) (Pitch) (Poles) Slotted/Phillips

(Color):GN:(Green), BK:(Black), BU:(Blue), RD:(Red), GY:(Gray)
 OG:(Orange), WT:(White), YL:(Yellow), CR:(Clear)

NAME: **DORABO** 宁波地博电气有限公司
 Ningbo Dorabo Electric CO., Ltd

APPD: J.Ting Chen 2022.11.25

CHKD: Duck Moo 2022.11.25

DRAFT: Steven Lu 2022.11.25

DB128L-5.08-XXP-C-S

SIZE: A4

TYPE: CUSTOMER_DRAWING

SCALE: 1:1

REV: T0-1

SHEET: 1/1