






NOTES:

1. MATERIAL:
 - HOUSING: LCP UL94V-0, BLACK
 - CONTACT: C5210R-EH, T=0.20mm
2. DURABILITY TEST: 100 CYCLES MIN.
3. SPECIFICATION:
 - DIELECTRIC STRENGTH: AC 300V/MINUTE
 - INSULATOR RESISTANCE: 500 Mohm MIN
 - CONTACT RESISTANCE: 40 mohm Max.
 - OPERATING TEMPERATURE: -40° ~ +85°



			GENERAL TOLERANCE		制图 DRAWING		深圳市富港科技有限公司			
			DIM	TOL	审核 CHECK					
			X.X	±0.30	批准 APPROVAL		产品名称 TITLE	光模块连接器	版本 REV.	A
1			初版发行		比例 SCALE		产品料号 PART NO.	FG-SFP-20P	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle		±3.0°	投影 Projection	材料 MATERIAL		页次 SHEET	1/1