




This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.



Customer drawing



Cover



With Insulator Support



Strain Relief

Dimensions

Positions	A	B	C	E	F
9	30.81	24.99	16.33	11.08	10.16
15	39.20	33.30	24.70	19.39	17.78
25	53.05	47.04	38.40	33.24	30.48
37	69.40	63.50	54.80	49.86	45.72

REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
1	HK--	First Release Drawing	09/01/08	IP
2	HK--	Update the Drawing	11/28/13	IP

D-SUB TECHNICAL DATA

BODY : Glass-Filled Thermoplastic PBT, UL94V-0
CONTACTS : Copper alloy
Gold flash over 50u" nickel on mating area
100u" tin over 50u" nickel on solder area
ELECTRICAL : Voltage rating 250 VAC/Rms 60Hz
Current Rating :3 AMP
Withstanding Voltage >1000 VAC Rms
Insulation resistance >1000 M Ohms
Contact resistance 20 mOhms max

PRODUCT CODE

L 17D X FR B XX S

L: RoHS Compliance

17D: Flash gold contact plating

Shell Size:E,A,B,C

Flat ribbon cable type

Contact type:
S=Socket

Configuration:
09,15,25,37

Type:
B=All plastic

UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVAL		DATE
U.S.	METRIC	DRAWN	PELIS LIA	11/28/13
.X +/-	0.50	CHECKED	Tony Tang	11/28/13
.XX +/-	0.30	CHECKED		
.XXX +/-	0.20			
FRACTIONS +/-				
ANGLES +/-	5°			
FOR MATERIALS AND FINISHES SEE NOTES		DRAWING FILE :		
REMOVE SHARP EDGES		ANGLE OF PROJECTION		
DIMENSIONS				
U.S.	INCHES			
METRIC	MM			

Amphenol

Amphenol East Asia Limited

TITLE
IDC flat cable D-SUB series

SIZE	DRAWING NO.	REV.
A4	C L17DXFRBXXS	2
SCALE	NONE	SHEET 1 OF 1