



PANEL CUT-OUT		
Z	Y	X
0.70~1.25	12.90~13.10	18.9~19.1
1.25~2.00	12.90~13.10	19.1~19.2
2.00~3.00	12.90~13.10	19.3~19.4

NOTES:

1. Rating:
CQC 6A 250VAC 6(8)A 250VAC
8A/128A 250VAC T105/55
UL CUL 10GPA 125VAC
6GPA 250VAC T105/55
VDE ENEC 6(4)A 250VAC T85/55
KC 6(4)A 250VAC T85/55
2. Circuit Diagram: 2P ON-OFF
3. Terminal Strength: $\geq 80N$
4. Electrical life: ≥ 10000 cycles
5. Withstand Voltage: Withstand Voltage: 1500VAC 1min
Terminals to Button: 3000VAC 1min
6. Leakage Current: 1mA
7. Current resistance: $\leq 50m\Omega$ (initial)
8. Insulation resistance: $\geq 100M\Omega$
9. Body Material: NYLON 66 94V-2~0

SWITCHING CIRCUIT



普通公差:
COMMON TOLERANCE:

UP TO 5	± 0.20
ABOVE 5 TO 30	± 0.30
ABOVE 30	± 0.50
ANGULAR	$\pm 5^\circ$

深圳市富港科技有限公司

单位 UNIT	mm	投影 PROJECTED		品名 PRODUCT NAME	船型开关	比例 SCALE	Free
绘图 DRAWN BY		校对 CHECKED BY		型号 MODEL NO.	FG-RS601A-1010011BB-6A		
日期 DATE		核准 APPROVAL BY		图号 DWG. NO.			

A4		
A3		
A2		
A1		
REV.	DATE	REVISION DESCRIPTION