


推荐插头尺寸



P.C.B LAYOUT

SPECIFICATION

1. Rating : DC 24V 3A.
2. Contact resistance: $\leq 70\text{m}\Omega$.
3. Insulation resistance: $\geq 100\text{M}\Omega$ (DC250V).
4. Withstanding voltage: 250VAC .
5. Insertion and extraction force: 3-30N.
6. life test: 5,000 cycles.
7. Operation temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
8. Sign "*" is importance dimension.

PIN	ø2.0	ø2.5
APPD.	✓	

					TOLERANCE UNLESS SPECIFIED								
7	COVER	SUS	1	NATURAL	<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°	A0	2024.8.9	首次发行		YKH		
6	COAT	PHOSPHOR BRONZE	1	Sn-PLATED			NO	DATE	REVISIONS		BY	APPD	
5	HOUSING	PA9T	1	BLACK									
4	FLAT PIECE	BRASS	1	Sn-PLATED									
3	CURVE PIECE	BRASS	1	Sn-PLATED	TITLE: DC JACK				UNIT : MM	ROHS	DWN		
2	SPRING	PHOSPHOR BRONZE	1	Sn-PLATED	MODEL: DC-044A-2.0-09				SCALE: 1:1	COMPLIANT	CHK'D		
1	PIN	BRASS	1	Sn-PLATED	 DONGGUANG HAORYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司				APPD				
NO.	PART NAME	MATERIAL	QTY	FINISHING					PRO.AGL: 		REV :A0		