










1	INNER SHELL	STAINLESS STEEL 316	--
2	OUTER SHELL	STAINLESS STEEL 304	NI PLATED
3	EMC	STAINLESS STEEL 316	—
4	MID PLATE	STAINLESS STEEL 301	NI PLATED
5	HOUSING	PA9T	BLACK UL 94V-0
6	TERMINALS	COPPER ALLOY C7025	Au1u" PLATED ON CONTACT AREA Tin PLATED ON SOLDER AREA
7	O-RING	RUBBER	BLACK
NO.	PARTS	MATERIAL	REMARKS



PCB REFERENCE DIAGRAM
TOLERANCE:±0.05



SCALE: 1:1	UNIT: mm
SIZE: A4	

Unless otherwise	
General Tolerance:	
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.10
Y°	±5°

Title:	Horizontal Type-C 24P Female SMT Pad up0.77 CH=2.2 L=10.05mm
--------	---

Molde Code: GT-USB-7108A

DRAWN	CHECKED	APPROVED	DATE
Xia	Chen	Chen	2025.01.19

G-Switch USB-C Specification:

- 1.Current rated: 5A on vbus/1.25A on vconn/0.25A on other
Voltage rating: 24V AC
- 2.Withstanding voltage: 100V AC/minute
- 3.Contact resistance: 40mΩ Max
- 4.Insulation resistance: 100MΩ Min
- 5.Operating temperature: -40°C ~ +85°C
- 6.Mating force: 5N~20N
- 7.Unmating force: 8N~20N,after durability test: 6N~20N
- 8.Durability cycle: 10,000 cycles
- 9.Data transmission rate up to 10Gbps
- 10.Waterproof grade: IP-X7

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND	TX1+	TX1-	VBUS	CC1	D+	D-	SBU1	VBUS	RX2-	RX2+	GND
First	Second	Second	First	Second	Second	Second	Second	First	Second	Second	First
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
GND	RX1+	RX1-	VBUS	SBU2	D-	D+	CC2	VBUS	TX2-	TX2+	GND
First	Second	Second	First	Second	Second	Second	Second	First	Second	Second	First

 品赞科技
www.dg-switch.com

REV: A0 SHEET: 1/1