


Product Summary

- V_{DS} -30V
- I_D -6.5A
- $R_{DS(ON)}$ (at $V_{GS}=10V$) < 45m Ω
- 100% EAS Tested
- 100% ∇V_{DS} Tested




General Description

- Trench Power MOSFET technology
- Excellent package for heat dissipation
- High density cell design for low $R_{DS(ON)}$
- Moisture Sensitivity Level 1
- Epoxy Meets UL 94 V-0 Flammability Rating
- Halogen Free

Applications

- Power switching application
- Uninterruptible power supply
- DC-DC convertor
- Motor drivers



P-Channel MOSFET

Absolute Maximum Ratings $(T_A = 25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Rating	Unit
V_{DSS}	Drain-Source Voltage	-30	V
V_{GSS}	Gate-Source Voltage	± 20	
I_D^*	Continuous Drain Current	-6.5	A
I_{DM}^*	Pulsed Drain Current	-20	
I_S^*	Diode Continuous Forward Current	-2	A
T_J	Maximum Junction Temperature	150	$^\circ\text{C}$
T_{STG}	Storage Temperature Range	-55 to 150	
P_D^*	Power Dissipation for Single Operation	2	W
		0.8	
$R_{\theta JA}^*$	Thermal Resistance-Junction to Ambient	62.5	$^\circ\text{C}/\text{W}$

Note: *Surface Mounted on 1in² pad area, $t \leq 10\text{sec}$.

Ordering Information

Order number	Package	Marking	Operation Temperature Range	MSL Grade	Ship, Quantity	Green
AO4953	SOP-8	4953	-55 to 150 $^\circ\text{C}$	1	T&R,3000	Rohs

Electrical Characteristics ($T_A = 25^\circ\text{C}$ unless otherwise noted)





Symbol	Parameter	Test Condition	AO4953			Unit
			Min.	Typ.	Max.	
Static Characteristics						
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_{DS}=250\mu A$	-30	-	-	V
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS}=-24V, V_{GS}=0V$	-	-	-1	μA
		$T_J=85^\circ C$	-	-	-30	
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_{DS}=250\mu A$	-1	-1.5	-2.3	V
I_{GSS}	Gate Leakage Current	$V_{GS}=\pm 20V, V_{DS}=0V$	-	-	± 100	nA
$R_{DS(ON)}^a$	Drain-Source On-state Resistance	$V_{GS}=-10V, I_{DS}=-6.5A$	-	36	45	m Ω
		$V_{GS}=-4.5V, I_{DS}=-5.6A$	-	50	65	
V_{SD}^a	Diode Forward Voltage	$I_{SD}=-1.7A, V_{GS}=0V$	-	-0.8	-1.3	V
Gate Charge Characteristics^b						
Q_g	Total Gate Charge	$V_{DS}=-15V, V_{GS}=-10V, I_{DS}=-4.9A$	-	11.6	16	nC
Q_{gs}	Gate-Source Charge		-	1.3	-	
Q_{gd}	Gate-Drain Charge		-	2.5	-	
Dynamic Characteristics^b						
R_G	Gate Resistance	$V_{GS}=0V, V_{DS}=0V, F=1MHz$	-	8	-	Ω
C_{iss}	Input Capacitance	$V_{GS}=0V, V_{DS}=-15V, \text{Frequency}=1.0MHz$	-	625	-	pF
C_{oss}	Output Capacitance		-	100	-	
C_{rss}	Reverse Transfer Capacitance		-	60	-	
$t_{d(ON)}$	Turn-on Delay Time	$V_{DD}=-15V, R_L=15\Omega, I_{DS}=-1A, V_{GEN}=-10V, R_G=6\Omega$	-	6	12	ns
t_r	Turn-on Rise Time		-	12	23	
$t_{d(OFF)}$	Turn-off Delay Time		-	25	46	
t_f	Turn-off Fall Time		-	6	12	
t_{rr}	Reverse Recovery Time	$I_{DS}=-4.9A, di_{SD}/dt=100A/\mu s$	-	14	-	ns
Q_{rr}	Reverse Recovery Charge		-	5	-	nC

Notes:





 a : Pulse test ; pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$.

b : Guaranteed by design, not subject to production testing.

Typical Characteristics




Typical Characteristics (Cont.)




Typical Characteristics (Cont.)

Drain-Source On Resistance




T_j - Junction Temperature ($^{\circ}\text{C}$)

Source-Drain Diode Forward




$-V_{SD}$ - Source-Drain Voltage (V)

Capacitance





$-V_{DS}$ - Drain-Source Voltage (V)

Gate Charge





Q_G - Gate Charge (nC)

Avalanche Test Circuit and Waveforms




Switching Time Test Circuit and Waveforms



Package Information

SOP-8



COMMON DIMENSIONS			
UNITS MEASURE=MILLIMETER			
SYMBOL	MIN	NOM	MAX
A	1.350	---	1.750
A1	0.100	---	0.250
A2	1.350	---	1.550
b	0.330	---	0.510
c	0.170	---	0.250
D	4.700	---	5.100
E	3.800	3.900	4.000
E1	5.800	---	6.200
e	1.270BSC		
L	0.400	---	1.270
theta	0°	--	8°

Unit:mm