



A		B		C		D		E	
REV.	DESCRIPTION				ECN NO.	NAME	DATE		



可打K脚, 50k起订

- 技术指标(Technical Index):
1. 温度范围(Temperature range): -25°C~+85°C.
 2. 额定电压(Rated voltage): 250V, AC.
 3. 额定电流(Rated current): 3.0A AC, DC.
 4. 接触电阻(Contact resistance): ≤20mΩ.
 5. 耐压值(Withstanding voltage): 1000V AC/minute.
 6. 绝缘电阻(Insulation resistance): ≥1000MΩ.

Part No	CKT	A	B
B3B-XH-A-2PZZ-MR	2	2.5	7.5
B3B-XH-A-3PZZ-MR	3	5.0	10.0
B3B-XH-A-4PZZ-MR	4	7.5	12.5
B3B-XH-A-5PZZ-MR	5	10.0	15.0
B3B-XH-A-6PZZ-MR	6	12.5	17.5
B3B-XH-A-7PZZ-MR	7	15.0	20.0
B3B-XH-A-8PZZ-MR	8	17.5	22.5
B3B-XH-A-9PZZ-MR	9	20.0	25.0
B3B-XH-A-10PZZ-MR	10	22.5	27.5
B3B-XH-A-11PZZ-MR	11	25.0	30.0
B3B-XH-A-12PZZ-MR	12	27.5	32.5
B3B-XH-A-13PZZ-MR	13	30.0	35.0
B3B-XH-A-14PZZ-MR	14	32.5	37.5
B3B-XH-A-15PZZ-MR	15	35.0	40.0
B3B-XH-A-16PZZ-MR	16	37.5	42.5




序号	品名	材质
1	XH2.5直针WTB胶芯	LCP UL94V-0 米色 白色
2	XH2.5直针WTB端子	铜合金/表面镀锡
3	XH2.5立式吸盖	LCP UL94V-0 米色




GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD	
DIM. x. x.xx GENERAL ANGLE: x°	TOL. ±0.50 ±0.20 ±0.10 ±1°	TITLE: XH2.5 直针WTB
	DWG. NO.: B3B-XH-A-XPZZ-MR	CHECKED: MAX
	PART NO.: B3B-XH-A-XPZZ-MR	DRAWN: ELLA
	UNIT: mm	SCALE: none
	SHEET: 1 of 1	DWG. SIZE: A4
	LAYER: bxcn	APPROVED: WILL




REV.	DESCRIPTION	ECN NO.	NAME	DATE



- NOTE(注):
- 1.10 SPROCKET HOLE PITCH CUMULATIVE TOLERANCE $\pm 0.2\text{mm}$. (10片孔距累积公差 $\pm 0.2\text{mm}$.)
 2. CARRIER CAMBER NOT TO EXCEED 1mm IN 100mm. (载带拱/弧度MAX:1/100mm.)
 3. ALL DIMENSIONS MEET EIA-481 REQUIREMENTS. (所有尺寸要满足协会EIA-481规范.)
 4. MATERIAL: CLEAR ANTISTATIC PS, COLD SEALING. (载带材料: 透明抗静电 PS, 冷封.)
 5. THICKNESS: $0.50 \pm 0.05\text{mm}$. (载带厚度: $0.50 \pm 0.05\text{mm}$.)
 6. PACKING LENGTH PER REEL: 6.43 METERS. (每卷包装长度: 6.43米.)
 7. COMPONENT LOAD PER REEL: 500 PCS. (每卷包装数量: 500片.)
 8. 纸箱装箱以不超过装箱线为准, 空余位置用塑料泡沫及保尼龙填充.
 9. 纸箱分小、中、标准型3种规格型号: 装箱为整箱(左下包装量)采用标准型纸箱包装, 未达到整箱数量以产品量适当采用小型或中型纸箱包装.




纸箱型号 Carton Type	小型 Small Size	中型 Medium	标准型 Standard
高度 Height (CM)	7.5	15	32



CKT (2.5mm pitch)	B0	W	F	S
	2	7.80	24	11.50 ± 0.10
3	10.30			
4	12.80			
5	15.30	32	14.20 ± 0.10	28.40
6	17.80			
7	20.30			
8	22.80			
9	25.30	44	20.20 ± 0.10	40.40
10	27.80			
11	30.30			
12	32.80	56	26.2 ± 0.10	52.40
13	35.30			
14	37.80			
15	40.30			
16	42.80			

CKT (2.5mm pitch)	W	PCS/REEL	REEL/CARTON	SUM(PCS)
2	24	500	10	5000
3				
4				
5	32	500	8	4000
6				
7				
8	44	500	6	3000
9				
10				
11	56	500	5	2500
12				
13				
14				
15				
16				



可打K脚, 50k起订

GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD	
DIM. x. TOL. x.x ± 0.50 x.x ± 0.25 x.xx ± 0.15 GENERAL ANGLE: x° $\pm 1^\circ$	TITLE: XH2.5 直针WTB载带包装	
	DWG. NO.: B3B-XH-A-XPZZ-MR	CHECKED: MAX
	PART NO.: B3B-XH-A-XPZZ-MR	DRAWN: ELLA
UNIT: mm	SCALE: none	SHEET: 1 of 1
DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL

BXCONN[®]

