

MF72 5D-5

NTC thermistors for inrush current limiting




Electrical Characteristics (Ta=25°C Unless otherwise specified)

PARAMETER	Symbol	CONDITION	VALUE	UNIT
Rated Zero-Power Resistance	R ₂₅	T _a =25°C ±0.2°C	5±20%	Ω
B Constant (Material Constant)	B _{25/85}	25°C /85°C	2500±10%	K
Max. steady State current	I _{max}	/	1	A
Max Shock Capacity	C _T	240V ac	68	μF
Thermal Dissipation Constant	δ	stationary in the air	6 typ	mW/°C
Thermal Time Constant	τ	stationary in the air	20 typ	sec
Residual Resistance	/	Max.steady State current	0.429	Ω
Operating Temperature Range	/	/	-40 to + 130	°C

Component Materials

Wrapper	Down-lead	Coating color
Modified phenolic resin	CP Wire	Black

Physical Dimensions (mm)

				
Inside Type	Outside Type	Straight Type		
Note: Default inside type for long lead.				
D (Max mm)	L (Min. mm)	d (mm)	T (Max. mm)	P (mm)
7.0	15.0	0.6±0.1	5.0	5.0±1.0

Ordering Information

Part Number	DELIVERY MODE	MPQ(PCS)
MF72 5D-5	Bulk	1,000

Electrical Test

Items	Test Methods and Remarks
Nominal Zero-Power Resistance at 25°C	Ambient temperature: $25 \pm 0.2^\circ\text{C}$;
Nominal B Constant	Measure the resistance at the ambient temperature of $25 \pm 0.05^\circ\text{C}$, $50 \pm 0.05^\circ\text{C}$ or $85 \pm 0.05^\circ\text{C}$. $B(25/50^\circ\text{C}) = \frac{\ln R_{25} - \ln R_{50}}{1/T_{25} - 1/T_{50}} \quad B(25/85^\circ\text{C}) = \frac{\ln R_{25} - \ln R_{85}}{1/T_{25} - 1/T_{85}}$
Thermal Time Constant	The total time for the temperature of the thermistor to change by 63.2% of the difference from ambient temperature T_0 ($^\circ\text{C}$) to T_1 ($^\circ\text{C}$) by the drastic change of the power applied to thermistor from Non-zero Power to Zero-Power state, normally expressed in second(S)
Dissipation Factor	The required power which makes the NTC thermistor body temperature raise 1°C through self-heated, normally expressed in milliwatts per degree Celsius (mW/ $^\circ\text{C}$) . It can be calculated by the following formula: $\delta = \frac{W}{T - T_0}$

Reliability Test

Items	Test Conditions & Methods	Requirements
Tensile strength of terminals	Gradually applying the force specified and duration $10 \pm 1\text{s}$ Leads Diameter : $0.5 < d \leq 0.8$, Pull: 10N Leads Diameter : $0.8 < d \leq 1.25$, Pull: 20N	No visible damage, $R_{25} \Delta R/R \leq \pm 25\%$
Solderability	The leads are immersed in a tin fluid 6mm from the thermistor. The tin fluid temperature is $245 \pm 5^\circ\text{C}$, and the dip soldering time is 2s to 3s.	The solder is evenly coated on the surface of the lead immersed part, and the tin area is over 95%.
Solder resistance	Leads are immersed in a tin fluid at a distance of 6mm from the thermistor. The tin fluid temperature is $260 \pm 5^\circ\text{C}$, the dip soldering time is $10\text{s} \pm 1\text{s}$.	No visible damage, $R_{25} \Delta R/R \leq \pm 25\%$
Thermal shock	Temperature: $-40 \pm 5^\circ\text{C}$, 30min / cycle, interval time 5min; temperature: $+130 \pm 5^\circ\text{C}$, 30min / cycle, interval time 5min; 5 cycles	No visible damage, $R_{25} \Delta R/R \leq \pm 25\%$
High temperature storage	Temperature: $130 \pm 5^\circ\text{C}$, time: $1000 \pm 24\text{h}$	No visible damage, $R_{25} \Delta R/R \leq \pm 25\%$
Steady state damp heat	Temperature: $-40 \pm 2^\circ\text{C}$, 90 ~ 95% RH, time: $1000 \pm 24\text{h}$	No visible damage, $R_{25} \Delta R/R \leq \pm 25\%$
Maximum steady state current Life test	$25 \pm 5^\circ\text{C}$, Maximum steady state current, $1000 \pm 24\text{hrs}$	No visible damage, $R_{25} \Delta R/R \leq \pm 25\%$
Endurance	$25 \pm 5^\circ\text{C}$, Maximum steady state current , Capacitance at 240Vac , 1min on / 5 min off , 1000 cycles	No visible damage, $R_{25} \Delta R/R \leq \pm 25\%$
Insulation resistance	Test voltage 500VDC, duration 1min	No visible damage, $R_{25} \Delta R/R \leq \pm 25\%$

Environmental Specification

Storage temperature:	-10°C to $+40^\circ\text{C}$
Storage Conditions:	Light-proof, Hermetically Sealed, Moisture-proof; The components should be left in their original packing to avoid soldering problems due to oxidized contacts.
Relative humidity:	$< 75\% \text{ RH}$
Storage period	The components should be employed within 12 months after delivery, the components should be resealed after opening the packing.

● Electrical Characteristics (Ta=25°C Unless otherwise specified)

Items	Characteristic Description	Characteristic curve
Derating Curve of I _{max}	When the applied ambient temperature of the product is lower than 0 °C or higher than 25 °C , the maximum allowable working current I _{max} should be reduced, and the amount of reduction is shown in the curve below.	Maximum rated current(%) Ambient temperature(°C) Remarks: T_L=Minimum temperature(°C) T_U=Maximum temperature(°C) The graph shows a trapezoidal derating curve. The y-axis is 'Maximum rated current(%)' with a mark at 100. The x-axis is 'Ambient temperature(°C)' with marks at T_L, 0, 25, and T_U. The curve starts at (T_L, 0), rises linearly to (0, 100), remains constant at 100% until 25°C, and then falls linearly to (T_U, 0).
R-T Characteristic Curve	R-T characteristic is the relationship between zero-power resistance and bodu temperature of the thermistor . The resistance value of the NTC thermistor is measured under a current with a sufficiently low spontaneous heat.	Resistance Temperature The graph shows the resistance-temperature characteristic. The y-axis is 'Resistance' with a mark at 25°C. The x-axis is 'Temperature' with marks at -50°C, 0°C, 25°C, 50°C, 100°C, 150°C, and 200°C. A red horizontal line is drawn at the 25°C resistance level, and a red vertical line is drawn at the 25°C temperature level, intersecting on the curve.
V-I Static Characteristic curve	In regions with low current, as the current gradually increases, the voltage of the ohmic contact also gradually rises. By dissipating heat from the surface of the thermistor and other parts, the self-heating caused by the current flow does not lead to an increase in the resistance temperature. However, when the heat generation is large, the temperature of the thermistor itself rises and the resistance value decreases. In such regions, the proportional relationship between current and voltage no longer holds.	Voltage (v) Current (mA) (25°C in Air) The graph shows the static V-I characteristic at 25°C in air. The y-axis is 'Voltage (v)' and the x-axis is 'Current (mA)'. The curve starts at the origin, rises to a peak, and then gradually decreases, showing a non-linear relationship.