




Detail I  
Scale 2:1



3D View



RECOMMENDED PCB LAYOUT  
TOLERANCE:±0.05MM  
(FOR REFERENCE ONLY)

NOTES:

1:MATERIAL

1-1: SUS-301 THICKNE=0.15MM

2:SPECIFICATIONS

2-1: RATED CURRENT: 1.0A

2-2: VOLTAGE RATING: 5.0V

2-3: CONTACT RESISTANCE: 50MΩ/MAX

2-4:COLMPING FPRCE: 60-120G

2-5:CLNSERTION FORCE:1000G

2-6:HOLDING FORCE:100G

2-7: WELDING THRUST: ≥3KG

2-8: OPERATING TEMPERATURE: -40°C~+85°C

3:DURABILITY: 200 CYCLES

4:SALT SPRAY TIME: 24H

5:ELECTROPLATE: THE NICKEL-PLATED SUBSTRATE IS 50u" MIN

6:REQUIREMENTS



6-1:TERMINAL TO EAT FULL TIN,NOTPEELING,  
WELDING OBVIOUS COLOR AND OTHED ADVERSE

6-2:ROHS、REACH、HF HALOGER ADVERSE OF DOMESTIC  
AND INTERNATIONAL ENVIRONMNTAL REQUIREMENTS




深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X: ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 屏蔽夹 L4.40*W0.80*H0.80	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HVCW-PBJX08BX	MOLD NO.
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HVC-2604020921	SHEET NO. 1 OF 1




Carton Size  
290\*330\*4 K3K



Carton Size  
345\*345\*360 K=K



The Carrier Tape Is Cold-Sealed  
And The Peeling Angle Of The  
Cold-Sealing Cover Tape Is 165°~180°.



Detail I  
Scale 2:1



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 包装图	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	
			SHEET NO.	1 OF 1