



30V/5.1A N Channel Advanced Power MOSFET**Features**

- Low $R_{DS(on)}$ @ $V_{GS}=10V$
- 3.3V Logic Level Control
- N Channel SOT23 Package
- Pb-Free, RoHS Compliant

Applications

- DC-to-DC converters
- Power management in battery-driven portables
- Low-side load switch and charging switch for portable devices
- Switching circuits
- High-speed line driver

$V_{(BR)DSS}$	$R_{DS(ON)}$ Typ	I_D Max
30V	32mΩ @10V	5.1A
	35mΩ @4.5V	

**Order Information****SOT23**

Product	Package	Marking	Packing
3400B	SOT23	A09T	3000PCS/Reel

Absolute Maximum Ratings

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

Symbol	Parameter	Rating	Unit	
Common Ratings (TA=25°C Unless Otherwise Noted)				
VGS	Gate-Source Voltage	±16	V	
V(BR)DSS	Drain-Source Breakdown Voltage	30	V	
TJ	Maximum Junction Temperature	150	°C	
TSTG	Storage Temperature Range	-50 to 150	°C	
Mounted on Large Heat Sink				
IDM	Pulse Drain Current Tested①	TA =25°C	20.4	A
ID	Continuous Drain Current	TA =25°C	5.1	A
		TA =70°C	4	
PD	Maximum Power Dissipation	TA =25°C	1.5	W
		TA =70°C	0.9	
RθJA	Thermal Resistance Junction-Ambient	80	°C/W	

Symbol	Parameter	Condition	Min	Typ	Max	Unit
Static Electrical Characteristics @ T _J = 25°C (unless otherwise stated)						
V _{(BR)DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V I _D =250pA	30	--	--	V
I _{DSS}	Zero Gate Voltage Drain Current(T _A =25°C)	V _{DS} =30V, V _{GS} =0V	--	--	1	pA
	Zero Gate Voltage Drain Current(T _A =125°C)	V _{DS} =24V, V _{GS} =0V	--	--	100	uA
I _{GSS}	Gate-Body Leakage Current	V _{GS} =±16V, V _{DS} =0V	--	--	±100	nA
V _{GS(TH)}	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =250pA	0.5	0.9	1.2	V
R _{DS(ON)}	Drain-Source On-State Resistance②	V _{GS} =10V, I _D =4A	--	32	40	mΩ
R _{DS(ON)}	Drain-Source On-State Resistance②	V _{GS} =4.5V, I _D =3A	--	35	45	mΩ
R _{DS(ON)}	Drain-Source On-State Resistance②	V _{GS} =3.3V, I _D =2A	--	38	50	mΩ
Dynamic Electrical Characteristics @ T _J = 25°C (unless otherwise stated)						
C _{iss}	Input Capacitance	V _{DS} =15V, V _{GS} =0V, f=1MHz	--	240	--	pF
C _{oss}	Output Capacitance		--	35	--	pF
C _{rss}	Reverse Transfer Capacitance		--	30	--	pF
Q _g	Total Gate Charge	V _{DS} =15V I _D =4A, V _{GS} =4.5V	--	3.1	--	nC
Q _{gs}	Gate Source Charge		--	0.4	--	nC
Q _{gd}	Gate Drain Charge		--	1.3	--	nC
Switching Characteristics						
t _{d(on)}	Turn on Delay Time	V _{DD} =15V, I _D =1A, R _G =3.3Ω, V _{GS} =10V	--	4.4	--	ns
t _r	Turn on Rise Time		--	2.6	--	ns
t _{d(off)}	Turn Off Delay Time		-	25.5	--	ns
t _f	Turn Off Fall Time		--	3.3	--	ns
Source Drain Diode Characteristics						
I _{SD}	Source drain current(Body Diode)	T _A = 25 °C	--	--	1.8	A
V _{SD}	Forward on voltage②	T _J =25°C, I _{SD} =4A, V _{GS} =0V	--	0.85	1.2	V

Notes: ① Pulse width limited by maximum allowable junction temperature

②Pulse test ; Pulse width≤300μs, duty cycle≤2%.

Typical Characteristics




Fig1. Typical Output Characteristics




Fig2. Normalized Threshold Voltage Vs. Temperature




Fig3. Typical Transfer Characteristics




Fig4. On-Resistance vs. Drain Current and Gate




Fig5. Typical Source-Drain Diode Forward Voltage




Fig6. Maximum Safe Operating Area

Typical Characteristics




Fig7. Typical Capacitance Vs. Drain-Source Voltage




Fig8. Typical Gate Charge Vs. Gate-Source Voltage




Fig9. Normalized Maximum Transient Thermal Impedance





Fig10. Switching Time Test Circuit and waveforms

SOT23 Mechanical Data



DIMENSIONS (unit : mm)

Symbol	Min	Typ	Max	Symbol	Min	Typ	Max
A	0.90	1.01	1.15	A ₁	0.01	0.05	0.10
b _p	0.30	0.42	0.50	c	0.08	0.13	0.15
D	2.80	2.92	3.00	E	1.20	1.33	1.40
e	--	1.90	--	e ¹	--	0.95	--
H _E	2.25	2.40	2.55	L _p	0.30	0.42	0.50
Q	0.45	0.49	0.55	v	--	0.20	--
w	--	0.10	--				

Notice

1. All product, product specifications and data are subject to change without notice to improve.

The right to explain is owned by CCX electronics company.

2. Confirm that operation temperature is within the specified range described in the product specification. Avoid applying power exceeding normal rated power; exceeding the power rating under steady-state loading condition may negatively affect product performance and reliability.
3. CCX shall not be in any way responsible or liable for failure induced under deviant condition from what is defined in this document.