







RoHS

目錄
MAPX

設變內容
MODIFICATION

日期
DATE



RECOMMENDED P.C.B. LAYOUT TOLERANCE UNSPECIFIED ±0.05mm

NOTE:
备注:

1.MATERIAL SPECIFICATION:

1.材料规格:

1-1.HOUSING:HIGH TEMPERATURE RESISTANT PLASTIC,UL94 V-0.

1-1. 胶芯材料: 高温塑胶, 防火等级UL94 V-0

1-2.TERMINAL: COPPER ALLOY

1-2. 端子材料: 铜合金

1-3.FRONT SHELL: STAINLESS STEEL

1-3. 外壳材料: 不锈钢

1-4.MID PLATE: COPPER ALLOY

1-4. 中夹片: 铜合金

2.PLATING SPECIFICATION:

2.电镀规格:

2-1.TERMINAL:

2-1. 端子:

Ni 30u" MIN. UNDER PLATED OVER ALL.

镀镍底 30u" MIN.

Au PLATED Golden Flash OVER Ni

表面刷金 Golden Flash

2-2.FRONT SHELL:

2-2. 外壳:

Ni 30u" MIN. PLATED OVER ALL.

镀镍底 30u" MIN.

3.MECHANICAL PERFORMANCE,

3.机械性能:

3-1.INSERTION FORCE: 0.5~2.0kgf.

3-1. 插入力: 0.5~2.0kgf.

3-2.REMOVAL FORCE: 0.6kgf~2.0kgf.

3-2. 拔出力: 0.6kgf~2.0kgf.

3-3.DURABILITY: 5000 CYCLES.

3-3. 插拔寿命: 5000次.

4.ELECTRICAL PERFORMANCE,

4.电气性能:

4-1. VOLTAGE RATING: 5.0V DC/AC

4-1. 额定电压: 5.0V DC/AC

CURRENT RATING: 2.0A

额定电流: 2.0A

4-2. LLCR: 50m"/PIN MAX.

4-2. 接触阻抗: 50mΩ/PIN MAX.

4-3.INSULATION RESISTANCE: 100M? MIN

4-3. 绝缘阻抗: 100MΩ MIN

4-4.DIELECTRIC WITHSTAND VOLTAGE,AC 100V FOR 1 MINUTE.

4-4. 耐电压: AC 100V FOR 1 MINUTE.

5. ENVIRONMENTAL PERFORMANCE:

5. 环境特性:

OPERATING TEMPERATURE: -25°C~+85°C.

工作温度: -25°C~+85°C.

PIN ASSIGNMENTS

A5	CC1	B12	GND				
A9	VBUS	B9	VBUS				
A12	GND	B5	CC2	L	L = 6.8	H	H = 1.0
PIN	SIGNAL NAME	PIN	SIGNAL NAME	L	L = 6.5	H	H = 0.6

产品图

PRODUCT CHART DWG



深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

公差一览表

TOLERANCE UNLESS OTHERWISE

X. ±0.35 X'. ±5'

.X ±0.30 .X' ±2'

.XX ±0.25 .XX' ±1'

.XXX ±0.10 .XXX' ±0.5'

单位
UNITS

MM

制图
DRAWING

Erick

产品料号
PRODUCT PART NO.

918-468K2023S40004

比例
SCALE

1:1

审核
CHKD

L S S

产品名称
PRODUCT NO.

TYPE-C3.1母座板上6.5后两脚
插板LCP黑胶SMT 6PIN

日期
DATE

2021/03/10

核准
APPD

黄国荣

角法
VIEW

版本
VER

A0