



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A			2024.09.10	
A2	ECN-P-2026011501	(A2)X1		2026.01.15	



3D ()

SPECIFICATIONS

- Voltage rating:100V AC/DC
- Current rating:2A AC/DC
- Withstanding Voltage:800V AC/minute
- Temperature range:-40°C~+125°C
- Insulation resistance: 1000MΩ
- Contact resistance:≤10mΩ
- After environmental testing:≤20mΩ

PART NO.:

X2016 W R-XX-NO SN

Series No




Category:W-Wafer

Welding Board Angle:R-Stright 90°

Row No.Pin No:XX-02~20Pin

Material : NO-PA66;

Planting:Sn-Bright Tin Plating



P.C.B LAYOUT

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	2.00	6.10	10	18.00	22.10
03	4.00	8.10	11	20.00	24.10
04	6.00	10.10	12	22.00	26.10
05	8.00	12.10	13	24.00	28.10
06	10.00	14.10	14	26.00	30.10
07	12.00	16.10	15	28.00	32.10
08	14.00	18.10	16	30.00	34.10
09	16.00	20.10			

X2016WR-XX-NOSN	Nylon 66 UL 94V-0	Brass	Tin-Plated	X2016H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	
CHECKED	
APPROVED	

VIEW:

UNIT: mm/in

SIZE: A4

MODEL TYPE: 2.00mm Crimp Style Connectors
PART NO.: X2016WR-XX-NOSN
DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A2