



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A			2024.12.9	
A2	ECN-P-2026031701	②X2		2026.03.16	





- Specifications()
- 1.Voltage rating():DC 250V
 - 2.Current rating():3A AC/DC
 - 3.Withstanding voltage(): 800V AC/minute ②
 - 4.Insulation resistance(): 1000MΩ Min
 - 5.Contact resistance():≤20mΩ Max
 - 6.Temperature range():-40 ~+125



PART NO.:

X2081 W V-2xXX-N0 SN

Series No
 Category:W-Wafer
 Welding Board Angle:V-Stright 180°
 Row No.Pin No:2xXX-2X05~2x20P
 Material:N0-PA66 UL94V-0
 Plating:SN-Bright Tin Plated



Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2x05	8.00	12.00	2x13	24.00	30.00
2x06	10.00	14.00	2x14	26.00	32.00
2x07	12.00	16.00	2x15	28.00	34.00
2x08	14.00	18.00	2x16	30.00	36.00
2x09	16.00	20.00	2x17	32.00	38.00
2x10	18.00	22.00	2x18	34.00	40.00
2x11	20.00	24.00	2x19	36.00	42.00
2x12	22.00	26.00	2x20	38.00	44.00

X2081WV-2xXX-N0SN	PA66	Brass	X2081H
PART NO	Material	Material(Pin)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN
 CHECKED
 APPROVED

VIEW: UNIT: mm/in
 SIZE: A4

MODEL TYPE:
 2.0mm Crimp Style Connector
 PART NO.:
 X2081WV-2xXX-N0SN
 DWG NO.:

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A2