







规格说明: Specifications:

电气特性: Electrical:

接触阻抗: Change from initial value
30mΩ maximum耐电压: Dielectric Withstanding Voltage
500V AC AT seaLevoL绝缘电阻: Insulation Resistance:
100MEGA ohms MIN

物理性能: Mechanical:

插拔力: Connector Mate and Unmate Force
Insertion force: 4.5kgf(MAX)

Withdrawal force: 1.0kgf~4.0kgf

寿命测试: Durability: 5000cycles

3	SHELL	K7(高碳钢)/不锈钢SUS304	Ni PLATED
2	TERMINAL	COPPER ALLOY	Au/Tin PLATED
1	HOUSING	LCP/BLACK	UL94V-0
NO.	PART NAME	DESCRIPTION	REMARK



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X' ±0.5"		DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: HDMI A TYPE 正向沉板CL-0.8mm	
 UNIT: mm [inch]		CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW194-HDMI A19-198B
		APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
				DRAW NO:	HYC-2604281053
SCALE:1:1	SIZE: A4			SHEET NO.	1 OF 1

RECOMMEND P.C.B LAYOUT (THICKNESS 1.6mm)
(COMPONENT SIDE) TOLERANCE ±0.05mm