



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN


NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 2.0
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 2A AC DC
- 4.Insulation Resistance: 800M Ω Min
- 5.Contact Resistance: 20m Ω Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25 $^{\circ}$ ~+ 85 $^{\circ}$

Part No	Pin	A	B	C
JXT-PH2.0-2PWB-P43	2	2.00	8.00	6.80
JXT-PH2.0-3PWB-P43	3	4.00	10.00	8.80
JXT-PH2.0-4PWB-P43	4	6.00	12.00	10.80
JXT-PH2.0-5PWB-P43	5	8.00	14.00	12.80
JXT-PH2.0-6PWB-P43	6	10.00	16.00	14.80
JXT-PH2.0-7PWB-P43	7	12.00	18.00	16.80
JXT-PH2.0-8PWB-P43	8	14.00	20.00	18.80
JXT-PH2.0-9PWB-P43	9	16.00	22.00	20.80
JXT-PH2.0-10PWB-P43	10	18.00	24.00	22.80
JXT-PH2.0-11PWB-P43	11	20.00	26.00	24.80
JXT-PH2.0-12PWB-P43	12	22.00	28.00	26.80
JXT-PH2.0-13PWB-P43	13	24.00	30.00	28.80
JXT-PH2.0-14PWB-P43	14	26.00	32.00	30.80
JXT-PH2.0-15PWB-P43	15	28.00	34.00	32.80
JXT-PH2.0-16PWB-P43	16	30.00	36.00	34.80

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.30	X.° ±5°	PART NO. JXT-PH2.0-NPWB-P43		TITLE: WAFER 2.00 卧贴	
.XX ±0.20	X.X° ±3°				
.XXX ±0.10	X.XX° ±1°				
UNITS	mm	DESIGN: Ethan		 MANUFACTURE DWG	
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			
				SCALE N:A	SHEET 1/1

