

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

技术要求Specification:

- 1、材质Material: PA66 UL94V-0:
- 2、额定电流 Current rating:2.0A AC,DC
- 3、额定电压 Voltage rating:250V AC,DC
- 4、温度范围 Temperature range:-25℃to+85℃
- 5、接触电阻 Contact resistance:≤20mΩ
- 6、绝缘电阻Insulation resistance:≥1000MΩ
- 7、耐压Withstand voltage:500V AC/minute
- 8、塑件表面平整光洁,无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious glitches, bubbles, distortion, gate strain, lack of material and other undesirable phenomena.

Part No	Pin	A	B	C	D	E
JXT-HY2.0-2PJK-P11	2	2.00	4.70	2.30	1.00	0.60
JXT-HY2.0-3PJK-P11	3	4.00	6.70	2.30	1.00	0.60
JXT-HY2.0-4PJK-P11	4	6.00	8.70	4.30	1.70	1.00
JXT-HY2.0-5PJK-P11	5	8.00	10.70	4.30	1.70	1.00
JXT-HY2.0-6PJK-P11	6	10.00	12.70	8.30	5.90	1.95
JXT-HY2.0-7PJK-P11	7	12.00	14.70	10.30	7.90	1.95
JXT-HY2.0-8PJK-P11	8	14.00	16.70	12.30	9.90	1.95
JXT-HY2.0-9PJK-P11	9	16.00	18.70	12.30	9.90	1.95
JXT-HY2.0-10PJK-P11	10	18.00	20.70	12.30	9.90	1.95
JXT-HY2.0-11PJK-P11	11	20.00	22.70	16.30	13.90	1.95
JXT-HY2.0-12PJK-P11	12	22.00	24.70	16.30	13.90	1.95
JXT-HY2.0-13PJK-P11	13	24.00	26.70	16.30	13.90	1.95
JXT-HY2.0-14PJK-P11	14	26.00	28.70	16.30	13.90	1.95
JXT-HY2.0-15PJK-P11	15	28.00	30.70	16.30	13.90	1.95
JXT-HY2.0-16PJK-P11	16	30.00	32.70	16.30	13.90	1.95

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
X.X ±0.30	X.° ±1°	PART NO.	TITLE: HY2.0MM HOUSING			
.XX ±0.20		JXT-HY2.0-NPJK-P11				
.XXX ±0.10		DESIGN: Ethan	MANUFACTURE DWG			
UNITS	mm					
MATERILA	— — —	CHED: Olvia		SCALE	SHEET	
FINISH	— — —	APPD: Ava		N:A	1/1	