







2PIN



3PIN



PCB LAYOUT

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	PIN	A	B	C
JXT-MX1.25-2PCB-P43	2	1.25	7.65	3.05
JXT-MX1.25-3PCB-P43	3	2.50	8.90	4.30
JXT-MX1.25-4PCB-P43	4	3.75	10.15	5.55
JXT-MX1.25-5PCB-P43	5	5.00	11.40	6.80
JXT-MX1.25-6PCB-P43	6	6.25	12.65	8.05
JXT-MX1.25-7PCB-P43	7	7.50	13.90	9.30
JXT-MX1.25-8PCB-P43	8	8.75	15.15	10.55
JXT-MX1.25-9PCB-P43	9	10.00	16.40	11.80
JXT-MX1.25-10PCB-P43	10	11.25	17.65	13.05
JXT-MX1.25-11PCB-P43	11	12.50	18.90	14.30
JXT-MX1.25-12PCB-P43	12	13.75	20.15	15.55
JXT-MX1.25-13PCB-P43	13	15.00	21.40	16.80
JXT-MX1.25-14PCB-P43	14	16.25	22.65	18.05
JXT-MX1.25-15PCB-P43	15	17.50	23.90	19.30
JXT-MX1.25-16PCB-P43	16	18.75	25.15	20.55

NOTES:

- 1.BASE: PA6T
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.25
- 2.Voltage Rating: 125V AC DC
- 3.Current Rating: 1A AC DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.20	X.*±5°	PART NO.	TITLE:		
X.X±0.10	X.X°±3°	JXT-MX1.25-NPCB-P43	WAFER 1.25 超薄		
X.XX±0.05	X.XX°±1°	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia	 SCALE SHEET		
MATERILA	— — —	APPD: Ava			
FINISH	— — —		N:A 1/1		