









	02-10P	0.10	MAX
	11-16P	0.12	MAX



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 2.0
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 2A AC DC
- 4.Insulation Resistance: 800MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

Part No	Pin	A	B	C	D
JXT-HY2.0-2PWB-P43	2	2.00	8.00	2.50	4.90
JXT-HY2.0-3PWB-P43	3	4.00	10.00	2.50	6.90
JXT-HY2.0-4PWB-P43	4	6.00	12.00	5.00	8.90
JXT-HY2.0-5PWB-P43	5	8.00	14.00	7.00	10.90
JXT-HY2.0-6PWB-P43	6	10.00	16.00	9.00	12.90
JXT-HY2.0-7PWB-P43	7	12.00	18.00	11.00	14.90
JXT-HY2.0-8PWB-P43	8	14.00	20.00	13.00	16.90
JXT-HY2.0-9PWB-P43	9	16.00	22.00	15.00	18.90
JXT-HY2.0-10PWB-P43	10	18.00	24.00	17.00	20.90
JXT-HY2.0-11PWB-P43	11	20.00	26.00	19.00	22.90
JXT-HY2.0-12PWB-P43	12	22.00	28.00	21.00	24.90
JXT-HY2.0-13PWB-P43	13	24.00	30.00	23.00	26.90
JXT-HY2.0-14PWB-P43	14	26.00	32.00	25.00	28.90
JXT-HY2.0-15PWB-P43	15	28.00	34.00	27.00	30.90
JXT-HY2.0-16PWB-P43	16	30.00	36.00	29.00	32.90

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd	
X.X ±0.30	X.* ±5°	PART NO.	TITLE:
.XX ±0.20	X.X* ±3°	JXT-HY2.0-NPWB-P43	WAFER 2.00 卧贴带扣
.XXX ±0.10	X.XX* ±1°	DESIGN: Ethan	MANUFACTURE DWG
UNITS	mm	CHED: Olvia	
MATERILA	---	APPD: Ava	
FINISH	---		SCALE
			N:A
			SHEET
			1/1