



客户图



Note:

1: Material(材料) :

Barrel: Brass C3604 (针管: 黄铜 C3604)

Plunger: Brass C3604 (针头: 黄铜 C3604)

Spring: SUS304 (弹簧: SUS304)

2: Plating(电镀) :

Barrel: 3u' Au over 50~80u' Ni(针管: 镀金3u', 镍底50~80u'.)

Plunger: 3u' Au over 50~80u' Ni (针头: 镀金3u', 镍底50~80u'.)

Spring: No plated (弹簧: 不电镀)

3: Electrical(电气特性) :

Rated Current & Voltage: DC 12V;2A (额定电压&电流: 直流12V,2A)

Contact Resistance: 50 mohm Max. at working height.

接触电阻: 最大50毫欧 (在工作高度状态下)

4: Mechanical(机械性能) :

Force: 120g±20% at working height. (120g±20% 在工作高度)。

Durability: 10.000 cycles(min) (寿命: 10000次)

5: WorkTemperature(工作环境) :

Withstanding Higt Temperature: 280℃

Operational Temperature: -40℃~ +85℃

NO.	ECN NO.	DESCRIPTION	DATE
-----	---------	-------------	------

深圳市鑫探技术有限公司									
HTTP://WWW.XYZPOGOPIN.COM TEL:0755-28773277 FAX:0755-28891353									
鑫探 ZY									
SCALE:	N/A	UNIT	mm	THE UNMARKED TOLERANCE ARE AS BELOW :					
SHEET:	1 of 1	PROJECTION		LENGTH		ANGLE			
DATE:	2015.11.05	VER.	D.0	X.XX X.X X.	±0.05mm ±0.10mm ±0.20mm	X.XX X.X X.	±0.50° ±1.00° ±2.00°	CHECKED BY:	
								APPROVED BY:	
								DWG. NO.	YZ137915075F-01
				TITLE:				Pogo pin 连接器	