







General tolerances(mm)

0 ~ 3	>3 ~ 6	>6 ~ 10	>10 ~ 18	>18 ~ 30	>30 ~ 50	>50 ~ 80	>80 ~ 120	>120 ~ 180	>180 ~ 250	>250 ~ 315	>315 ~ 400	>400 ~ 500	>500
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50

0.1/10

±2°




REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Product model	PIN	A	B
JXT-EDGKR-5.08-2P1G	2	11.66	5.08
JXT-EDGKR-5.08-3P1G	3	16.74	10.16
JXT-EDGKR-5.08-4P1G	4	21.82	15.24
JXT-EDGKR-5.08-5P1G	5	26.90	20.32
JXT-EDGKR-5.08-6P1G	6	31.98	25.40
JXT-EDGKR-5.08-7P1G	7	37.06	30.48
.....			
JXT-EDGKR-5.08-24P1G	24	5.08xN+1.5	5.08X(N-1)

UL Standard	B	C	D
Rated Voltage(V)/Current(A)	300/15	/	300/10
IEC Standard			
Overvoltage Category/Pollution Degree	Ⅲ/3	Ⅲ/2	Ⅱ/2
Rated Voltage(V)/Current(A)	/	320/20	/
Withstanding voltage(V/1Min)	AC2000		
Torque Tightening(N·m/Lb·in)	M2.5, 0.4/3.54		
Wire Range(rigid and flexible)(mm ² /AWG)	0.2~2.5/28~12		
Pitch(mm)/Poles	5.08/N=02~24P		
Stripping length(mm)	7-8		
Operating temperature(°C)	-40~+105		
Conform to RoHS	Yes		

5	Screws	Steel	M2.5/Zn Plated
4	Cage	Copper alloy	Ni plated
3	Pin	Copper	Sn plated
2	Cover	PA66	UL94V-0
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
		PART NO. JXT-EDGKR-5.08-NP1G		TITLE: Socket-type terminal		
UNITS	mm	DESIGN: Ethan		MANUFACTURE DWG		
MATERILA	— — —	CHED: Olvia				
FINISH	— — —	APPD: Ava				
					SCALE N:A	SHEET 1/1