








REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

技术要求Specification:

1. 材质Material: PA66 UL94V-0:
2. 额定电流 Current rating:2.0A AC,DC
3. 额定电压 Voltage rating:100V AC,DC
4. 温度范围 Temperature range:-25℃to+85℃
5. 接触电阻 Contact resistance:≤20mΩ
6. 绝缘电阻Insulation resistance:≥1000MΩ
7. 耐压Withstand voltage:800V AC/minute
8. 塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrs, bubbles.distortion, gate strain, lack of material and other undesirable phenomena.

Part No	Pin	A	B	C
JXT-PH2.0-2PJK-P11	2	2.00	5.70	4.50
JXT-PH2.0-3PJK-P11	3	4.00	7.70	6.50
JXT-PH2.0-4PJK-P11	4	6.00	9.70	8.50
JXT-PH2.0-5PJK-P11	5	8.00	11.70	10.50
JXT-PH2.0-6PJK-P11	6	10.00	13.70	12.50
JXT-PH2.0-7PJK-P11	7	12.00	15.70	14.50
JXT-PH2.0-8PJK-P11	8	14.00	17.70	16.50
JXT-PH2.0-9PJK-P11	9	16.00	19.70	18.50
JXT-PH2.0-10PJK-P11	10	18.00	21.70	20.50
JXT-PH2.0-11PJK-P11	11	20.00	23.70	22.50
JXT-PH2.0-12PJK-P11	12	22.00	25.70	24.50
JXT-PH2.0-13PJK-P11	13	24.00	27.70	26.50
JXT-PH2.0-14PJK-P11	14	26.00	29.70	28.50
JXT-PH2.0-15PJK-P11	15	28.00	31.70	30.50
JXT-PH2.0-16PJK-P11	16	30.00	33.70	32.50

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X ±0.30	X.* ±1°	PART NO.	TITLE:	
.XX ±0.20		JXT-PH2.0-NPJK-P11	PH2.0MM HOUSING	
.XXX ±0.10		DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		SCALE
MATERILA	---	APPD: Ava		SHEET
FINISH	---			N:A
				1/1