


0402ESDA-36N

ESD Protection Diode

Features

- Deal ESD protection for high frequency, low voltage applications.
- Exceeds testing requirements outlined in IEC 61000-4-2
- Ultra low capacitance (2pF typ.)
- Very low leakage current
- Fast response time
- Bi-directional

Package



Applications

- High Speed Data Ports (USB 2.0, IEEE 1394)
- Computers & Peripherals (Cell phone, PDA, HDTV, DVD players)
- Surface mount
- RoHS Compliant

Mechanical Data

Ordering information

Order code	Package	Base qty	Delivery mode
0402ESDA-36N	0402	10k	Tape and reel

Absolute Maximum Rating

Rating	Symbol	Value	Units
ESD per IEC 61000-4-2 (Contact)	V_{ESD}	± 8	KV
ESD per IEC 61000-4-2 (Air)		± 15	
Response time	T_{RISE}	<0.5	ns
Lead content	—	<1000	ppm
Withstanding ESD capability	IEC61000-4-2	Level 4	—
Operating Ambient Temperature	T_A	-50 to + 85	°C
Storage Temperature	T_{stg}	-50 to + 125	°C



0402ESDA-36N

ESD Protection Diode


Electrical Characteristics

Part NO.	Working Voltage	Varistor ¹ voltage measured	Maximum ² ESD allowable clamping Voltage	Leakage ³ Current (at Initial State)	Leakage ³ Current (after ESD Test)	Typical Cap.Value at 1MHz
Symbol	$V_{DC(max.)}$	$V_{trigger}$	V_C	I_{LDC}	I_{LDCA}	C
Unit	V	V	V	μA	μA	pF
0402ESDA-36N	36	100~150	<200	<0.1	<1.0	2~4.5

Notes:

- 1 The varistor voltage was measured at 1 mA current
- 2.The Clamping voltage was measured at 8*20 us standard current.
- 3.The Leakage current was measured at working voltage.

ESD Wave Form



Electrical Characteristics

SEVERITY LEVEL	AIR DIRCHARGE	DIRECT DISCHARGE
1	2KV	2KV
2	4KV	4KV
3	8KV	6KV
4	15KV	8KV


Note:IEC61000-4-2 compliant ESD current pulse waveform.



0402ESDA-36N

ESD Protection Diode

Soldering Parameters



IR reflow Pb free process suggestion profile

- (1) The solder recommend is Sn96.5/Ag3.5 and thickness recommend as shown in table 5.3.
- (2) Ramp-up rate (217°C to peak) + 3°C /second max.
- (3) Temp. maintain at 175±25°C 180 seconds max.
- (4) Temp. maintain above 217°C 60~150 seconds.
- (5) Peak temperature range 245 +20/-10°C within 5°C of actually peak temperature (tp) 10~20 seconds.
- (6) Ramp down rate -6°C/second max.

Environment Reliability Test


Characteristic	Test Method and Description			
High Temperature Storage	The specimen shall be subjected to 125±2°C for 1000±2 hours without load and then stored at room temperature and normal humidity for one or two hours. The change of varistor voltage shall be within 10%.			
Temperature Cycle	The temperature cycle of specified temperature shall be repeated five times and then stored at room temperature and normal humidity for one or two hours. The change of varistor voltage shall be within 10% and mechanical damage shall be examined.	Step	Temperature	Period
		1	-40±3°C	30±3min
		2	room temperature	1 hour
		3	125±3°C	30±3min
High Temperature Load	After being continuously applied the maximum allowable voltage at 85±2°C for 1000±2 hours, the specimen shall be stored at room temperature and normal humidity for one or two hours. The change of varistor voltage shall be within 10%.			
Damp Heat Load/Humidity Load	The specimen should be subjected to 40±2°C and 90~95% RH, the maximum allowable voltage applied for 1000±2 hours and then stored at room temperature and normal humidity for one or two hours. The change of varistor voltage shall be within 10%.			
Low Temperature Storage	The specimen should be subjected to -40±2°C for 1000±2 hours without load and then stored at room temperature and normal humidity for one or two hours. The change of varistor voltage shall be within 10%.			



0402ESDA-36N


ESD Protection Diode

Outline Drawing




SYMBOL	MILLIMETERS		
	0201	0402	0603
L	0.60±0.03	1.00±0.10	1.60±0.15
W	0.30±0.03	0.50±0.10	0.80±0.10
P	0.15±0.05	0.25±0.10	0.30±0.10
H	0.30±0.03	0.60(Max.)	0.90(Max.)

Packaging Tape



SYMBOL	MILLIMETER
	0402
A0	0.62±0.05
B0	1.12±0.05
K0	0.60±0.05
D	1.55 ^{+0.1} _{-0.05}
P	2.00±0.10
P2	2.00±0.10
P0	4.00±0.10
W	8.00±0.10
E	1.75±0.10
F	3.50±0.05

Packaging Reel



SYMBOL	MILLIMETER
	0402
A	178±1
B	60±0.5
C	13.0±0.2
D	21±0.2
E	2.0±0.5
W	9.0±0.5
W1	1.5±0.1
Quantity	10000PCS

