

Operation: SMT 贴片式/二档位 正拨 中小型 拨动开关**LTEM NO.:** MS-209C (Three D)

(L7.15×W4.00×H2.10 SLIDE-SWITCH)

SLIDE-SWITCH

Technical parameter

PROJECT	LEVEL	A[better product]	B[average product]
Electrical Properties	Contact Rating	0.3A, 24V DC	
	Initial Contact Resistance	30mΩ max.	50mΩ max.
	Insulation Resistance	100MΩ min.500V DC	Skey/PD: 100MΩ min.300V DC
	Withstand Voltage	500V AC for 1 minute	350 V AC for 1 minut
Durable Performance	There No Load	15,000 Cycles	10,000 Cycles
	Rated Load	12,000 Cycles	8,500 Cycles
	Storage temp.	-35℃~+75℃(Operating Temp:)	

表面贴装 SMT






正向操作 LATERAL

精密部品 NICETY

可靠 STABILIZE

適合環保 RoHS

Unit:mm




Operating Force

Inward
Exiting $2.5 \pm 0.5\text{N}$ (1N.=100gram-force) $2.5 \pm 0.5\text{N}$ (1N.=100gram-force)

Solder-ability (Max.)

IR Reflow: 255°C, 5sec.


Manual: 350°C, 3sec.



Pin Definition


Material declaration

No.	NAME	Type	Description
① A	拨柄 STEM	1	PA6T (Black)耐高温尼龙
② B	盖板 COVER	1	不锈钢 SUS304 t=0.4mm
③ C	基座 BOTTOM	1	PA6T (Black)耐高温尼龙
④ D	簧片 CONTACT	2	磷铜 C5210 G/F
⑤ E	嵌件 TERMINALS	6	黄铜 C2680(Qsn6.5-01 镀银) t-0.30



■ 回流方式的参考举例

1. 加热方式远红外线加热的上下加热方式。
2. 温度测量方式用 V0.1 ~ V0.2 的 CA(K) 或 CC(T) 进行测量。
3. 温度分布



邀您使用(微信)小程序

硕方电子开关&连接器选型手册

手机扫码即可进入...

本品不屬於危害性廢棄物,須丟棄時可以委託
回收商予以回收再生處理。
Products do not belong to •

注記 NOTICE

1. 碩方公司擁有最終解釋權; The company reserves the right of final interpretation;
2. 文件禁止外洩、轉載; Leaked and reproduced prohibited;
3. 未經授權修改無效。Modify is invalid.

運送時本產品不要直接與水、酸鹼性化學物質接觸,或放置於含有以上氣體環境中,並且需要注意會有滑落、側翻的危險發生; 運輸過程中不能有碰撞或者擠壓,須保證溫度與濕度適中 [常溫 25°C, 濕度在 50°C 以內], 不可導致材料變形或氧化。