



P-DUKE POWER

FED40 Series

DC-DC Converter
Up to 40Watts

3

YEARS
WARRANTY

ROHS
COMPLIANT

REACH
COMPLIANT



Automation



Datacom



IPC



Industry



Measurement



Telecom



Automobile



Boat



Charger



Medical



PV



Railway

UL US CB CE UK CA

1600
VDC
Isolation
Voltage

2 : 1
Input
Range

6
sided
Shielding

LOW
Standby
Power

NO
Min. Load
Required

REMOTE
ON
OFF

OCP

OTP

OVP

SCP

UVP

PART NUMBER STRUCTURE

FED40	-	48	S	05	-	M3	N	HC
Series Name		Input Voltage (VDC)	Output Quantity	Output Voltage (VDC)		Operating Temp. Options	Remote Control Options	Assembly Options
		12:9~18 24:18~36 48:36~75	S:Single	3P3:3.3 05:5 12:12 15:15 24:24		☐ : Standard -40~+105°C With derating M3: M3 Version -55~+105°C With derating	☐ : Positive logic N: Negative logic	☐ : None HC: 7G-0020C-F; H=0.22" (※NRND) HC1: 7GA0120P01-F; H=0.3" HC2: 7GA0121P01-F; H=0.5" HC3: 7GA0122P01-F; H=0.8"
			D:Dual	12:±12 15:±15 24:±24				※NRND: Not recommended for new designs

TECHNICAL SPECIFICATION All specifications are typical at nominal input, full load and 25°C unless otherwise noted

Model Number	Input Range	Output Voltage	Output Current @Full Load	Input Current @ No Load	Efficiency	Maximum Capacitor Load
	VDC	VDC	mA	mA	%	μF
FED40-12S3P3	9 ~ 18	3.3	10000	20	90	26600
FED40-12S05	9 ~ 18	5	8000	20	91	20000
FED40-12S12	9 ~ 18	12	3333	20	91	3900
FED40-12S15	9 ~ 18	15	2666	20	91	2600
FED40-12S24	9 ~ 18	24	1666	20	91	1300
FED40-12D12	9 ~ 18	±12	±1666	20	90	± 2600
FED40-12D15	9 ~ 18	±15	±1333	20	91	± 1600
FED40-12D24	9 ~ 18	±24	±833	20	91	±650
FED40-24S3P3	18 ~ 36	3.3	10000	15	91	26600
FED40-24S05	18 ~ 36	5	8000	15	92	20000
FED40-24S12	18 ~ 36	12	3333	15	92	3900
FED40-24S15	18 ~ 36	15	2666	15	92	2600
FED40-24S24	18 ~ 36	24	1666	15	91	1300
FED40-24D12	18 ~ 36	±12	±1666	15	90	± 2600
FED40-24D15	18 ~ 36	±15	±1333	15	91	± 1600
FED40-24D24	18 ~ 36	±24	±833	15	91	±650
FED40-48S3P3	36 ~ 75	3.3	10000	10	91	26600
FED40-48S05	36 ~ 75	5	8000	10	92	20000
FED40-48S12	36 ~ 75	12	3333	10	92	3900
FED40-48S15	36 ~ 75	15	2666	10	92	2600
FED40-48S24	36 ~ 75	24	1666	10	92	1300
FED40-48D12	36 ~ 75	±12	±1666	10	91	± 2600
FED40-48D15	36 ~ 75	±15	±1333	10	91	± 1600
FED40-48D24	36 ~ 75	±24	±833	10	90	±650

INPUT SPECIFICATIONS

Parameter	Conditions		Min.	Typ.	Max.	Unit
Operating input voltage range		12Vin(nom)	9	12	18	VDC
		24Vin(nom)	18	24	36	
		48Vin(nom)	36	48	75	
Start up voltage		12Vin(nom)			9	VDC
		24Vin(nom)			18	
		48Vin(nom)			36	
Shutdown voltage		12Vin(nom)	7	8	8.8	VDC
		24Vin(nom)	15	16	17.5	
		48Vin(nom)	32	33.5	35	
Start up time	Constant resistive load	Power up		60		ms
		Remote ON/OFF		60		
Input surge voltage	1 second, max.	12Vin(nom)			25	VDC
		24Vin(nom)			50	
		48Vin(nom)			100	
Input filter					Pi type	
Remote ON/OFF	Referred to –Vin pin	Positive logic (Standard)	DC-DC ON		Open or 3 ~ 12VDC	mA
			DC-DC OFF		Short or 0 ~ 1.2VDC	
		Negative logic (Option)	DC-DC ON		Short or 0 ~ 1.2VDC	
			DC-DC OFF		Open or 3 ~ 12VDC	
		Input current of Ctrl pin	-0.5		0.5	
		Remote off input current		3		mA

OUTPUT SPECIFICATIONS						
Parameter	Conditions		Min.	Typ.	Max.	Unit
Voltage accuracy			-1.0		+1.0	%
Line regulation	Low Line to High Line at Full Load		-0.2		+0.2	%
Load regulation	No Load to Full Load	Single	-0.5		+0.5	%
		Dual	-1.0		+1.0	
Cross regulation	Asymmetrical load 25%/100% FL	Dual	-5.0		+5.0	%
Voltage adjustability	Single output	3.3Vout, 5Vout, 12Vout 15Vout, 24Vout	-10 -10		+10 +20	%
Ripple and noise	Measured by 20MHz bandwidth With a 0.1μF/50V X7R MLCC	3.3Vout, 5Vout 12Vout, 15Vout 24Vout		75 100 150	100 125 200	mVp-p
Temperature coefficient			-0.02		+0.02	%/°C
Transient response recovery time	25% load step change			250		μs
Over voltage protection	Zener diode clamp	3.3Vout 5Vout 12Vout 15Vout 24Vout		3.9 6.2 15 20 30		VDC
Over load protection	% of Iout rated; Hiccup mode			150		%
Short circuit protection			Continuous, automatics recovery			


GENERAL SPECIFICATIONS						
Parameter	Conditions		Min.	Typ.	Max.	Unit
Isolation voltage	1 minute	Input to Output Input (Output) to Case	1600 1600			VDC
Isolation resistance	500VDC		1			
Isolation capacitance					1500	pF
Switching frequency			225	250	275	kHz
Safety approvals	IEC/ EN/ UL62368-1				UL:E193009 CB:UL(Demko)	
Case material					Copper	
Base material					FR4 PCB	
Potting material					Silicone (UL94 V-0)	
Weight					32g (1.13oz)	
MTBF	MIL-HDBK-217F, Full load.				1.066 x 10 ⁶ hrs	

ENVIRONMENTAL SPECIFICATIONS						
Parameter	Conditions		Min.	Typ.	Max.	Unit
Operating ambient temperature	Standard M3 Version	With derating With derating	-40 -55		+105 +105	°C
Maximum case temperature					105	
Over temperature protection				115		°C
Storage temperature range			-55		+125	°C
Thermal impedance		Without Heat-sink With Heat-sink		10.8 10.3 9.3 7.7 6.2		°C/W
		HC				
		HC1				
		HC2				
		HC3				
Thermal shock					MIL-STD-810F	
Shock					MIL-STD-810F	
Vibration					MIL-STD-810F	
Relative humidity					5% to 95% RH	


EMC SPECIFICATIONS			
Parameter	Conditions		Level
EMI	EN55032	With external components.	Class A + Class B
EMS	EN55035		
ESD	EN61000-4-2	Air $\pm 8\text{kV}$ and Contact $\pm 6\text{kV}$	Perf. Criteria A
Radiated immunity	EN61000-4-3	20 V/m	Perf. Criteria A
Fast transient	EN61000-4-4	$\pm 2\text{kV}$	Perf. Criteria A
	FED40-12□□□	With an aluminum electrolytic capacitor (Nippon chemi-con KY series, 220 μF /100V) and a TVS(SMDJ58A, 58V, 3000Watt peak pulse power) in parallel.	
	FED40-24□□□	With an aluminum electrolytic capacitor (Nippon chemi-con KY series, 220 μF /100V) and a TVS(SMDJ64A, 64V, 3000Watt peak pulse power) in parallel.	
	FED40-48□□□	With an aluminum electrolytic capacitor (Nippon chemi-con KY series, 220 μF /100V) and a TVS (SMDJ120A,120V, 3000Watt peak pulse power) in parallel.	
Surge	EN61000-4-5	$\pm 2\text{kV}$	Perf. Criteria A
	FED40-12□□□	With an aluminum electrolytic capacitor (Nippon chemi-con KY series, 220 μF /100V) and a TVS(SMDJ58A, 58V, 3000Watt peak pulse power) in parallel.	
	FED40-24□□□	With an aluminum electrolytic capacitor (Nippon chemi-con KY series, 220 μF /100V) and a TVS(SMDJ64A, 64V, 3000Watt peak pulse power) in parallel.	
	FED40-48□□□	With an aluminum electrolytic capacitor (Nippon chemi-con KY series, 220 μF /100V) and a TVS (SMDJ120A,120V, 3000Watt peak pulse power) in parallel.	
Conducted immunity	EN61000-4-6	10 Vr.m.s	Perf. Criteria A
Power frequency magnetic field	EN61000-4-8	100A/m continuous; 1000A/m 1 second	Perf. Criteria A

CAUTION: This power module is not internally fused. An input line fuse must always be used.


CHARACTERISTIC CURVE




FED40-48S05 Derating Curve



FED40-48S05 Efficiency VS Input Voltage



FED40-48S05 Efficiency VS Output Load



FED40-48S05 Derating Curve
With Heat-sink

FUSE CONSIDERATION

This power module is not internally fused. An input line fuse must always be used.


This encapsulated power module can be used in a wide variety of applications, ranging from simple stand-alone operation to an integrated part of sophisticated power architecture.

To maximum flexibility, internal fusing is not included; however, to achieve maximum safety and system protection, always use an input line fuse.

The input line fuse suggest as below :




Model	Fuse Rating (A)	Fuse Type
FED40-12□□□	8	Fast-Acting
FED40-24□□□	4	Slow-Blow
FED40-48□□□	2	Slow-Blow

The table based on the information provided in this data sheet on inrush energy and maximum DC input current at low Vin.

MECHANICAL DRAWING

PIN CONNECTION

PIN	SINGLE	DUAL
1	+ Vin	+ Vin
2	- Vin	- Vin
3	Ctrl	Ctrl
4	+ Vout	+ Vout
5	- Vout	Common
6	Trim	- Vout

- All dimensions in inch [mm]
Tolerance :x.xx±0.02 [x.x±0.5]
x.xxx±0.010 [x.xx±0.25]
- Pin dimension tolerance ±0.004[0.10]

RECOMMENDED PAD LAYOUT
Standard

-HC

-HC1 、 -HC2 、 -HC3


All dimensions in inch[mm]
Pad size(lead free recommended)
Through hole 1.2.3.4.5.6: $\Phi 0.051$ [1.30]
Top view pad 1.2.3.4.5.6: $\Phi 0.064$ [1.63]
Bottom view pad 1.2.3.4.5.6: $\Phi 0.102$ [2.60]

THERMAL CONSIDERATIONS

The power module operates in a variety of thermal environments.

However, sufficient cooling should be provided to help ensure reliable operation of the unit.

Heat is removed by conduction, convection, and radiation to the surrounding environment.


Proper cooling can be verified by measuring the point as the figure below.

The temperature at this location should not exceed "Maximum case temperature".

When operating, adequate cooling must be provided to maintain the test point temperature at or below "Maximum case temperature".


You can limit this temperature to a lower value for extremely high reliability.

- Thermal test condition with vertical direction by natural convection (20LFM).




HEAT-SINK TYPE OPTIONS


FED40-□□□□□-**HC**
7G-0020C-F




FED40-□□□□□-**HC1**
7GA0120P01-F



FED40-□□□□□-**HC2**
7GA0121P01-F



FED40-□□□□□-**HC3**
7GA0122P01-F



1. All dimensions in inch [mm]
2. Tolerance :x.xx±0.02 [x.x±0.5]
x.xxx±0.010 [x.xx±0.25]


OUTPUT VOLTAGE ADJUSTMENT

Output voltage set point adjustment allows the user to increase or decrease the output voltage set point of the module. This is accomplished by connecting an external resistor between the Trim pin and either the +Output or -Output pins. With an external resistor between the Trim and -Vout, the output voltage set point increases. With an external resistor between the Trim and +Vout, the output voltage set point decreases. The external Trim resistor needs to be at least 1/16W of rated power.

EXTERNAL OUTPUT TRIMMING

Output can be externally trimmed by using the method shown below.

Trim-up



☐ S3P3

ΔV (%)	1	2	3	4	5	6	7	8	9	10
Vout (V)	3.333	3.366	3.399	3.432	3.465	3.498	3.531	3.564	3.597	3.630
RU (k Ω)	57.93	26.165	15.577	10.283	7.106	4.988	3.476	2.341	1.459	0.753

☐ S05

ΔV (%)	1	2	3	4	5	6	7	8	9	10
Vout (V)	5.050	5.100	5.150	5.200	5.250	5.300	5.350	5.400	5.450	5.500
RU (k Ω)	36.57	16.58	9.917	6.585	4.586	3.253	2.302	1.588	1.032	0.588

☐ S12

ΔV (%)	1	2	3	4	5	6	7	8	9	10
Vout (V)	12.120	12.240	12.360	12.480	12.600	12.720	12.840	12.960	13.080	13.200
RU (k Ω)	367.91	165.95	98.636	64.977	44.782	31.318	21.701	14.488	8.879	4.391

☐ S15


ΔV (%)	1	2	3	4	5	6	7	8	9	10
Vout (V)	15.150	15.300	15.450	15.600	15.750	15.900	16.050	16.200	16.350	16.500
RU (k Ω)	419.81	199.91	126.60	89.95	67.96	53.30	42.83	34.98	28.87	23.98
ΔV (%)	11	12	13	14	15	16	17	18	19	20
Vout (V)	16.650	16.800	16.950	17.100	17.250	17.400	17.550	17.700	17.850	18.000
RU (k Ω)	19.98	16.65	13.83	11.42	9.32	7.49	5.87	4.43	3.15	1.99

☐ S24

ΔV (%)	1	2	3	4	5	6	7	8	9	10
Vout (V)	24.240	24.480	24.720	24.960	25.200	25.440	25.680	25.920	26.160	26.400
RU (k Ω)	1275.2	606.60	383.73	272.30	205.44	160.87	129.03	105.15	86.58	71.72
ΔV (%)	11	12	13	14	15	16	17	18	19	20
Vout (V)	26.640	26.880	27.120	27.360	27.600	27.840	28.080	28.320	28.560	28.800
RU (k Ω)	59.56	49.43	40.86	33.51	27.15	21.57	16.66	12.29	8.38	4.86

OUTPUT VOLTAGE ADJUSTMENT(CONTINUED)

Trim-down


☐ ☐ S3P3

ΔV (%)	1	2	3	4	5	6	7	8	9	10
Vout (V)	3.267	3.234	3.201	3.168	3.135	3.102	3.069	3.036	3.003	2.970
RD (k Ω)	69.47	31.235	18.49	12.117	8.294	5.745	3.924	2.559	1.497	0.647

☐ ☐ S05

ΔV (%)	1	2	3	4	5	6	7	8	9	10
Vout (V)	4.950	4.900	4.850	4.800	4.750	4.700	4.650	4.600	4.550	4.500
RD (k Ω)	45.533	20.612	12.306	8.152	5.66	3.999	2.812	1.922	1.23	0.676

☐ ☐ S12

ΔV (%)	1	2	3	4	5	6	7	8	9	10
Vout (V)	11.880	11.760	11.640	11.520	11.400	11.280	11.160	11.040	10.920	10.800
RD (k Ω)	460.99	207.95	123.6	81.423	56.118	39.249	27.199	18.162	11.132	5.509

☐ ☐ S15

ΔV (%)	1	2	3	4	5	6	7	8	9	10
Vout (V)	14.850	14.700	14.550	14.400	14.250	14.100	13.950	13.800	13.650	13.500
RD (k Ω)	284.89	128.68	76.61	50.58	34.96	24.55	17.11	11.53	7.19	3.72

☐ ☐ S24

ΔV (%)	1	2	3	4	5	6	7	8	9	10
Vout (V)	23.760	23.520	23.280	23.040	22.800	22.560	22.320	22.080	21.840	21.600
RD (k Ω)	838.15	376.78	222.98	146.09	99.95	69.19	47.22	30.74	17.93	7.68