



产品承认书 SPECIFICATION FOR APPROVAL

客户名称:

CUSTOMER

我司料号:

OUR PART NO.

XRPQ26-250412

我司品名:

OUR PART NAME

Transformer

送样日期:

DATE SAMPLES

数量:

QUANTITY

制造确认 MANUFACTURER APPROVE

拟制 DRAWN	审核 CHECKED	确认 APPROVED
Hufangting	RaoPing	ZhongCuilan

客户确认 CUSTOMER APPROVE

客户名称 CUSTOMER NAME:

客户料号 CUSTOMER P/N:

规格型号 DESCRIPTION:

PQ26 vertical 6+6 400uH

检查结果: 合格 不合格

签名及盖章:

INSPECT RESULT ACCEPT REJECT

SIGNATURE AND STAMP

说明 REMARK:

如对本承认书内容有异议请提出或标记发送至我司, 本承认书在未收到异议回复时于本承认书提供一周后生效。

If you have any objection to the contents of this acknowledgment, please raise it or send the mark to us. The acknowledgment will become effective one week after the acknowledgment is provided in the absence of any objection.

东莞市祥如电子有限公司

DONGGUAN XIANGRU ELECTRONICS CO.,LTD

Tel: 0769-86346548 Fax: 0769-86346358

Email: dgxiangru@126.com


产品承认书

SPECIFICATION FOR APPROVAL

客户名称 CUSTOMER		日期 DATE	2025/1/17
客户物料编号 CUSTOMER P/N		客户规格型号 DESCRIPTION	PQ26 vertical 6+6 400uH
我司物料编号 OUR PART NO	XRPQ26-250412	我司品名 OUR PART NAME	Transformer

一、外观尺寸 Appearance of size

单位 Unit: mm




A	B	C	D	E	F	H	
29.5max	24.0max	31.5max	3.5±0.5	25.0±0.5	3.8±0.3	0.7±0.1	

(以上尺寸为手工测量只做参考详细尺寸以实物为准) (The above dimensions are measured by hand for reference only. The detailed dimensions are subject to the physical objects.)


NOTE:

1. 骨架为PQ2620立式6+6(XHY-PQ-2620), 拔除PIN4.7.8.9脚, 成品剪PIN2脚2/3, PIN朝机台右顺转绕制(CNC);
 . The frame is a PQ2620 vertical 6+6 (XHY-PQ-2620); remove pins 4, 7, 8, and 9; trim 2/3 of pin 2; wind clockwise with the pins facing the right side of the machine (CNC);
2. 心球磁芯PQ27/20B, 材质PC40, 需开气隙, 气隙装于顶部, 平面磁芯用单层28mm胶带背胶2层;
 . PQ27/20B toroidal core, material PC40, requires an air gap; the air gap is located at the top; the flat core is secured with two layers of 28mm adhesive tape
3. 磁芯胶带用10mm胶带包3圈;
 Wrap the core with 10mm tape three times:
4. 产品真空含浸处理: 成品需二次焊锡: 成品沿磁芯包23mm胶带包2圈;
 Product vacuum impregnation: The finished product requires a second soldering: Wrap the finished product with 23mm tape around the magnetic core twice:
5. 产品胶带颜色为淡黄色: 产品标签贴于PIN1-6脚边: PQ2620-03 400uH BO JH
 The product tape is light yellow: The product label is affixed near pins 1-6: PQ2620-03 400uH BO JH

SCHEMATIC:



CONNECT





产品承认书 SPECIFICATION FOR APPROVAL

客户名称 CUSTOMER		日期 DATE	2025/1/17
客户物料编号 CUSTOMER P/N		客户规格型号 DESCRIPTION	PQ26 vertical 6+6 400uH
我司物料编号 OUR PART NO	XRPQ26-250412	我司品名 OUR PART NAME	Transformer

绕线结构 /WINDING STRUCTURE:

WDG	Pin S--F	Material	Turns	Tape	挡墙		套管		备注note
					PIN	TOP	S	F	
N1	3--2	2UEW Φ0.28mm*2P	28TS	2TS*10.0mm	/	/	22L*15MM		密绕 winding
N2	12--11	2UEW Φ0.4mm*2P	14TS	2TS*10.0mm	/	/	17L*15MM	17L*15MM	
N3	11--10	2UEW Φ0.4mm*2P	6TS	2TS*10.0mm	/	/	17L*15MM	17L*15MM	
N4	2--1	2UEW Φ0.28mm*2P	13TS	2TS*10.0mm	/	/		22L*15MM	
N5	5--6	2UEW Φ0.28mm*1P	9TS	2TS*10.0mm	/	/	28L*15MM	28L*15MM	中密绕

电气性能 /ELECTRICAL PROPERTIES (at 25°C):

半测电感 at 10KHZ 0.3V Half Measured Inductance at 10KHZ 0.3V				耐压测试 Pressure resistance test	绝缘电阻测试at DC500V Insulation resistance testat DC500V	圈数测试at 20KHZ 1V Lap Testat 20KHZ 1V	DCR测试25°C DCR test 25°C
foot position	minimum value	midpoint	maximum values				
3-1	380uH	400uH	420uH	P-S:8.75KV AC,50Hz,5mA,3S	P-S:100MΩ MIN	3-1:41TS	/
漏感测试 at 10KHZ 0.3V 短路其它脚Leakage Inductance Test at 10KHZ 0.3V Shorted Other Pins				P-C:1. 50KV AC, 50Hz, 5mA, 3S	P-C:100MΩ MIN	12-11:20TS± 0.5	
3-1	40uH MAX			C-S:1. 50KV AC, 50Hz, 5mA, 3S	S-C:100MΩ MIN	5-6:9TS±0.5	
成测电感 at 10KHZ 0.3V Measured Inductance at 10KHZ 0.3V							
foot position	minimum value	midpoint	maximum values	电弧侦测 arc detection	PIN短路测试 PIN short circuit test		
3-1	375uH	400uH	424uH				
				PIN3--44			

材料表 /MATERIAL LIST:

N0.	名称 ITEM	型号 TYPE	UL RATING	制造商 SUPPLERS	UL NO.	
1	CORE	PQ26	/	HAINING WANLI ELECTRONICS CO.,LTD	N/A	
2	BOBBIN	PHENOLIC T375H	94V0 150°C	CHANG CHUN PLASTICS CO LTD	E59481	
3	WIRE	2UEW 94V-0	QA-155°C	WU HU COPPER CORWV ELECTRICIAN LTD	E326270	
4	TAPE	JY312Y	130°C	HOU MAILADUONA ELECTRIC MATERIAL CO	E188295	
5	TIN	无铅107H	420°C	THOUSAND ISLAND METAL FOIL Co.,LTD.	N/A	
6	VARNISH	1032CJJ	155°C	QUALIPOLY CHEMICAL CORP	E213437	
7	TRIPLE WIRE	TIW-B	130°C	SHENZHEN HEDONG NEW MATERIAL CO LTD	VDE40038661	
制表 MADE		审核 CHECKED	批准 APPROVED			
Hufangting		RaoPing	ZhongCuilan			



注意事项 Matters needing attention

1、本公司产品适用于 AV 设备、OA 设备、家电、信息服务等一般电子设备中。

Our products are designed and promoted for use in general electronic devices such as audio-video equipment, office automation equipment, home appliance and information service.

2、当本公司的产品使用在一般电子设备以外的领域时，对于此所引发的设备失效我司将不承担任何法律责任。

In case of using the product for the purpose other than general electronics devices, we shall not be held liable for any dysfunctions in or damage to the equipment with which the product is used.

3、本承认书只保证我司产品作为一个单体时的质量情况，当我司产品被安装到贵公司产品上时，请贵司对使用在贵司电路上的产品情况进行了有效评价和确认。

Our specification limits the quality of the component as a single unit. Please ensure the component is thoroughly evaluated in your application circuit.

4、不要对产品施加过大的振动或机械冲击；

Do not apply excessive vibration or mechanical shock to products.

5、为防止断线，请不要使用锋利的物体接触线圈，如镊子；

Do not touch wire with sharp objects such as tweezers to prevent wire breakage.

6、在产品贴装时不要使用过大的压力，避免磁芯断裂。

Do not apply excessive stress to products mounted on boards to prevent core breakage.

7、为保证端子电极的焊接特性和包装材料处于良好状态，请于本公司发货后 6 个月内使用本产品。同时，由于端子电极的焊接特性会随时间发生变化，如果贮存时间超过 6 个月，请首先确认其焊接特性后再安装使用。

To maintain the solderability of terminal electrodes and to keep the packing material in good condition, product should be used within 6 months from the time of delivery. And the solderability of products electrodes may decrease as time passes, so in case of storage over 6 months, solderability shall be checked before actual usage.

8、存放货物的仓库应满足以下条件 Store products in a warehouse in compliance with the following condition:

条件 Conditions	元件含包装物 Packing status	元件自身 Component itself
温度 Temperature	-25~+40℃	-25~+85℃
湿度 Humidity	30~70%RH	30~70%RH

9、不要使产品遭受温度和湿度的快速变化。

Do not subject products to rapid changes in temperature and humidity.

10、不要将产品存放在化学环境中，如硫酸气体或碱性气体中，否则会降低电极端子的焊接特性和使电感器腐蚀。

Do not store the products in chemical atmosphere such as one containing sulfurous acid gas or alkaline gas, that will causes poor solderability and corrosion of inductors.

11、为了避免受潮气、灰尘等物质的影响，产品应保管于货架上。

Store products on pallets to protect from humidity, dust, etc

12、产品应避免热冲击、振动以及直接光照等等。

Avoid heat shock, vibration, direct sunlight, etc.