


Features

- Fast switching speed
- High conductance



Mechanical Data

- Case: SOT-23
- Molding Compound: UL Flammability Classification Rating 94V-0
- Terminals: Matte tin-plated leads; solderability-per MIL-STD-202, Method 208



Maximum Ratings (@ T_A = 25°C unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Repetitive Peak Reverse Voltage	V _{RRM}	250	V
Working Peak Reverse Voltage	V _{RWM}	200	V
DC Blocking Voltage	V _R	200	V
RMS Reverse Voltage	V _{R(RMS)}	141	V
Forward Continuous Current	I _F	200	mA
Non-Repetitive Peak Forward Surge Current, t = 8.3ms	I _{FSM}	2	A
Non-Repetitive Peak Forward Surge Current, t = 1ms	I _{FSM}	2.5	A

Thermal Characteristics

Parameter	Symbol	Value	Unit
Power Dissipation	P _D	250	mW
Thermal Resistance Junction-to-Air	R _{θJA}	500	°C/W
Thermal Resistance Junction-to-Case	R _{θJC}	310	°C/W
Operating Junction Temperature Range	T _J	-65 ~ +150	°C
Storage Temperature Range	T _{STG}	-65 ~ +150	°C

Electrical Characteristics (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Reverse Breakdown Voltage	$V_{(BR)R}$	$I_R = 100\mu\text{A}$	250	-	-	V
Forward Voltage	V_F	$I_F = 100\text{mA}$	-	-	1.00	V
		$I_F = 200\text{mA}$	-	-	1.25	V
Maximum Peak Reverse Current	I_R	$V_R = 200\text{V}, T_J = 25^\circ\text{C}$	-	-	0.1	μA
		$V_R = 200\text{V}, T_J = 100^\circ\text{C}$	-	-	15	μA
Total Capacitance	C_J	$V_R = 0\text{V}, f = 1.0\text{MHz}$	-	-	5	pF
Reverse Recovery Time	t_{rr}	$I_F = I_R = 10\text{mA}$ $I_{rr} = 0.1 \times I_R, R_L = 100\Omega$	-	-	50	ns

Ratings and Characteristics Curves (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)




Fig 1 Derating Curve




Fig 2 Derating Curve




Fig 3 Reverse Current vs. Junction Temperature




Fig 4 Surge Current Derating Curve




Fig 5 Typical Reverse Characteristic




Fig 6 Typical Forward Characteristics





Fig 7 Capacitance Characteristics

Package information

SOT-23 (Unit: mm)



Mounting Pad Layout (Unit: mm)

