

Operation: 焊线式 中型(单向)撬柄检测开关[操作力可定制]



ITEM NO.: TC-311M (Series)

(L8.0×W3.5×H10.6mm DETECTOR-SWITCH)

焊线式

正向操作 DOWN

精密部品

NICETY

STABILIZE

適合環保 RoHS


Technical parameter

PROJECT	LEVEL	A[better product]	B[average product]
Electrical Properties	Contact Rating	50mA, 12V DC	
	Initial Contact Resistance	50mΩ max.	
Durable Performance	Insulation Resistance	100MΩ min.500V DC Skey/PD: 100MΩ min.300V DC	
	Withstand Voltage	200V AC for 1 minute	100 V AC for 1 minut
Storage temp.	There No Load	75,000 Cycles	55,000 Cycles
	Rated Load	60,000 Cycles	45,000 Cycles
Operating Force		1.0N. (1N.=100gram-force)	
Operating temperature		(Operating Temp: -30℃~+75℃) IR Reflow:255℃,5sec. Manual:350℃,3sec.	






Material declaration

No.	NAME	Description
1	外壳	PA6T(Gray)耐热塑胶
2	按柄	PA6T(Gray)耐热塑胶
3	弹片	C5191R-H (t=0.15mm)磷青铜
4	弹簧	不锈钢 SUS304 【t=0.1mm】
5	压片	C5191R-H (t=0.15mm)磷青铜
6	基座	PA6T(Gray)耐热塑胶
7	端子	H62 (t=0.20mm)黄铜

Common terminal



Unit:mm



邀您使用(微信)小程序

碩方电子开关&连接器选型手册

手机扫码即可进入...