




HSF



RoHS



PCB LAYOUT

SPECIFICATION

Current Rating: 3.0 Amp
Insulation Resistance: 1000M ohms min
Contact Resistance: 20M ohms max
Dielectric Withstanding: AC500V
Operating Temperature: -65° C to +125° C
Contact Material: Brass
Insulator Material: PBT, UL 94V-0 Black

Ordering Code:

FHES11 - X - X - D - X - X - X
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No:
② No. of Contacts
02 To 80
③ Contact Plating:
G0:Gold flash S0:Selective E:PA9T
G1:3U" Gold S1:Selective 3U" Packing
G2:5u" Gold S2:Selective 5u" A:Tray
G3:10u" Gold S3:Selective 10u" B:Bag
G4:15u" Gold S4:Selective 15u" T:Tube
G5:30u" Gold S5:Selective 30u" U:Tube+CAP
④ SN: Tin Connector Type R: Tape&Reel
D: Dual W: Tape&Reel+CAP
⑤ Plastic High:
H: 8.5
Please mark the desired length in the H

⑥ Insulator Material

A: PBT
B: PA6T
C: LCP

D: PA46

E: PA9T

⑦ Packing

A: Tray

B: Bag

T: Tube


U: Tube+CAP

R: Tape&Reel

W: Tape&Reel+CAP

Unless Otherwise specified tolerance
X. ±0.35 X.XX: ±0.20
X.X: ±0.25 X.XXX: ±0.15

SCALE: As Shown UNIT: mm
DRAW YG ZHONG DATE 01/05/2016
CHECK BobYang DATE 01/05/2016



3rd ANGLE PROJECTION



ANTENK ELECTRONICS CO., LTD
Http://www.antenk.com
E-mail: sales@antenk.com

TITLE:

2.54mm Female Header Dual Row Straight Type(W=5.0 H=8.5)

DRAWING NO:

FHES11-XXDXXX

PRODUCT NO:

FHES11-XXDXXX

Update dimensional tolerance

03/10/2025

DESCRIPTION

DATE



REV