

## -30V/-10A P-Channel MOSFET

### Features


- Trench Power LV MOSFET technology
- High density cell design for Low  $R_{DS(ON)}$
- High Speed switching

### Product Summary

$V_{DS}$	$R_{DS(ON)}$ MAX	$I_D$ MAX
-30V	18m $\Omega$ @-10V	-10A
	30m $\Omega$ @-4.5V	


### Application

- Battery protection
- Power management
- Load switch




4435A : Device code  
XXXX : Code

Marking and pin assignment



SOP-8 top view




Schematic diagram




Absolute Maximum Ratings ( $T_A=25^{\circ}\text{C}$ unless otherwise noted)				
Symbol	Parameter	Rating	Unit	
<b>Common Ratings (<math>T_C=25^{\circ}\text{C}</math> Unless Otherwise Noted)</b>				
$V_{DS}$	Drain-Source Breakdown Voltage	-30	V	
$V_{GS}$	Gate-Source Voltage	$\pm 25$	V	
$T_J$	Maximum Junction Temperature	150	$^{\circ}\text{C}$	
$T_{STG}$	Storage Temperature Range	-50 to 155	$^{\circ}\text{C}$	
$I_S$	Diode Continuous Forward Current	$T_C=25^{\circ}\text{C}$ -10	A	
<b>Mounted on Large Heat Sink</b>				
$I_{DM}$	Pulse Drain Current Tested	$T_C=25^{\circ}\text{C}$ -50	A	
$I_D$	Continuous Drain Current	$T_C=25^{\circ}\text{C}$ -10	A	
$P_D$	Maximum Power Dissipation	$T_C=25^{\circ}\text{C}$ 3	W	
$R_{\theta JA}$	Thermal Resistance Junction-Ambient	42	$^{\circ}\text{C}/\text{W}$	

<b>Electrical Characteristics (T<sub>J</sub>=25°C unless otherwise noted)</b>						
<b>Symbol</b>	<b>Parameter</b>	<b>Condition</b>	<b>Min</b>	<b>Typ</b>	<b>Max</b>	<b>Unit</b>
<b>Static Electrical Characteristics @ T<sub>J</sub> = 25°C (unless otherwise stated)</b>						
BV <sub>(BR)DSS</sub>	Drain-Source Breakdown Voltage	V <sub>GS</sub> =0V, I <sub>D</sub> =-250μA	-30	--	--	V
I <sub>DSS</sub>	Zero Gate Voltage Drain Current	V <sub>DS</sub> =-30V, V <sub>GS</sub> =0V	--	--	-1	μA
I <sub>GSS</sub>	Gate-Body Leakage Current	V <sub>GS</sub> =±20V, V <sub>DS</sub> =0V	--	--	±100	nA
V <sub>GS(th)</sub>	Gate Threshold Voltage	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =-250μA	-1.0	-1.5	-3.0	V
R <sub>DS(on)</sub>	Drain-Source On-State Resistance	V <sub>GS</sub> =-10V, I <sub>D</sub> =-10A	--	13	18	mΩ
		V <sub>GS</sub> =-4.5V, I <sub>D</sub> =-8A	--	20	30	mΩ
<b>Dynamic Electrical Characteristics @ T<sub>J</sub> = 25°C (unless otherwise stated)</b>						
C <sub>ISS</sub>	Input Capacitance	V <sub>DS</sub> =-15V, V <sub>GS</sub> =0V, f=1MHz	--	1500	--	pF
C <sub>OSS</sub>	Output Capacitance		--	180	--	pF
C <sub>RSS</sub>	Reverse Transfer Capacitance		--	150	--	pF
<b>Switching Characteristics</b>						
Q <sub>g</sub>	Total Gate Charge	V <sub>DS</sub> =-10V, I <sub>D</sub> =-10A, V <sub>GS</sub> =-15V	--	29	--	nC
Q <sub>gs</sub>	Gate Source Charge		--	5.4	--	nC
Q <sub>gd</sub>	Gate Drain Charge		--	5.4	--	nC
t <sub>d(on)</sub>	Turn-on Delay Time	V <sub>DD</sub> =-15V, I <sub>D</sub> =-10A, V <sub>GS</sub> =-10V, R <sub>G</sub> =2.5Ω	--	10	--	nS
t <sub>r</sub>	Turn-on Rise Time		--	45	--	nS
t <sub>d(off)</sub>	Turn-Off Delay Time		--	55	--	nS
t <sub>f</sub>	Turn-Off Fall Time		--	60	--	nS
<b>Source- Drain Diode Characteristics</b>						
V <sub>SD</sub>	Forward on voltage	T <sub>J</sub> =25°C, I <sub>S</sub> =-10A	--	-0.8	-1.2	V


## Typical Operating Characteristics




**Fig1. Typical Output Characteristics**




**Fig2. Typical Gate Charge Vs. Gate-Source Voltage**




**Fig3. Normalized On-Resistance Vs. Temperature**



**Fig4. On-Resistance Vs. Drain-Source Current**




**Fig5. Maximum Safe Operating Area**



**Fig6. Typical Capacitance Vs. Drain-Source Voltage**

## SOP-8 Package information



Symbol	Dimensions in Millimeters(mm)		Dimensions In Inches	
	Min	Max	Min	Max
A	1.450	1.750	0.057	0.068
A1	0.100	0.250	0.003	0.009
A2	1.350	1.550	0.053	0.061
b	0.330	0.510	0.012	0.020
c	0.170	0.250	0.006	0.009
D	4.700	5.100	0.185	0.200
e	1.270(BSC)		0.050(BSC)	
E	3.800	4.000	0.149	0.157
E1	5.800	6.200	0.228	0.244
L	0.400	1.270	0.015	0.050
$\theta$	0°	8°	0°	8°