




Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE±0.05)



SPECIFICATIONS

Current Rating:3.0AMP

Contact Resistance:10mΩMax

Dielectric Strength:Min 1000V RMS

Operation Temperature:-40°c to +105°c

Contact Material:Brass

Accepted Pin:0.40 to 0.60mm

Insulator Material:Polyester(UL94V-0)

Standard: PPS

Soldering temperature: 260°C±5° 5S

TOLERANCE UNLESS OTHERWISE SPEC		SHENZHEN FUGANG TECHNOLOGY CO.,LTD			
BASIC DIMENSION	TOLERANCE	DSND	H	C	TITLE: ARRANGE THE FEMALES
x.x	±0.50	CHKD	L	P J	PART NO:FG-PM2.0-1-NP-H3.0-C
x.xx	±0.30	APVD	L	Z W	
x.xxx	±0.10				
ANGLES	±3°				
		UNIT:mm	SCALE:1:1	SIZE:A4	SHEET:1/1