



SPECIFICATIONS

Current Rating:3Amps
 Insulation Resistance:1000MΩ Min
 Contact Resistance:20mΩ Max
 Withstanding Voltage:AC 1000V
 Operation Temperature:-40° to +105°
 Contact Material:Brass
 Insulator Material: Polyester (UL 94V-0)
 Contact plating:Gold Flash
 Standard:PA6T
 Max. Processing Temp:240° C for30-60seconds
 (260° Cfor10seconds)

| P/N | PIN | DIM. A | DIM. B |
|--------------------|------|--------|--------|
| HMT-2.54-2*3P-ZJN | 2*3 | 5.08 | 7.62 |
| HMT-2.54-2*4P-ZJN | 2*4 | 7.62 | 10.16 |
| HMT-2.54-2*5P-ZJN | 2*5 | 10.16 | 12.70 |
| HMT-2.54-2*6P-ZJN | 2*6 | 12.70 | 15.24 |
| HMT-2.54-2*7P-ZJN | 2*7 | 15.24 | 17.78 |
| HMT-2.54-2*8P-ZJN | 2*8 | 17.78 | 20.32 |
| HMT-2.54-2*9P-ZJN | 2*9 | 20.32 | 22.86 |
| HMT-2.54-2*10P-ZJN | 2*10 | 22.86 | 25.40 |
| HMT-2.54-2*12P-ZJN | 2*12 | 27.94 | 30.48 |
| HMT-2.54-2*13P-ZJN | 2*13 | 30.48 | 33.02 |
| HMT-2.54-2*14P-ZJN | 2*14 | 33.02 | 35.56 |
| HMT-2.54-2*15P-ZJN | 2*15 | 35.56 | 38.10 |
| HMT-2.54-2*16P-ZJN | 2*16 | 38.10 | 40.64 |
| HMT-2.54-2*17P-ZJN | 2*17 | 40.64 | 43.18 |
| HMT-2.54-2*18P-ZJN | 2*18 | 43.18 | 45.72 |
| HMT-2.54-2*20P-ZJN | 2*20 | 48.26 | 50.80 |
| HMT-2.54-2*22P-ZJN | 2*22 | 53.34 | 55.88 |
| HMT-2.54-2*25P-ZJN | 2*25 | 60.96 | 63.50 |
| HMT-2.54-2*30P-ZJN | 2*30 | 73.66 | 76.20 |
| HMT-2.54-2*32P-ZJN | 2*32 | 78.74 | 81.28 |



| | | | |
|--|-----------|--|--|
| GENERAL TOLERANCES UNLESS SPECIFIED | |  深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd | |
| X.±0.30 | X.°±5° | PART NO. | TITLE: |
| .X±0.25 | .X°±1° | HMT-2.54-2*NP-ZJN | 2.54DC3-NPIn H8.9 180度 PC3.2 L11.5 6T |
| .XX±0.20 | .XX°±0.5° | DESIGN: James | CUSTOMER |
| MANUFACTURE DWG | | CHED: Talen | SIZE UNITS |
| | | APPD: Sophia | A4 MM |
| | | | SCALE SHEET |
| | | | N:A 1/1 |